





2695-NR



(1.55)
.061
TYP






2695-NRP




(.25)
.010
TYP 2

(1.02)
.040
TYP 2

(7.9)
.31
TYP 2
(FOR CKTS. 7 AND HIGHER)





SEE NOTE 6



SEE NOTE 7

2695 - N * *
NO. OF. CIRCUITS

OPTION CODE			
	RAMP	POLARIZING RIBS	MAT'L
BLANK	NO	NO	NOTE 1A
R	YES	NO	NOTE 1A
RP	YES	YES	NOTE 1A
RP-BK	YES	YES	NOTE 1B



NOTES:

- MATERIAL: A - NYLON, UL94V-0, COLOR: WHITE
B - NYLON, UL94V-0, COLOR: BLACK
- FINISH: SEE TERMINAL DRAWING
- THIS HOUSING CONFORMS TO MOLEX PRODUCT SPECIFICATION PS-10-07.
- PACKAGING: PER PK-2695-001
- HOUSING TO BE USED WITH CRIMP TERMINAL SERIES 2759, 6459, AND 41572. PARTS MADE AFTER 4/19/2012 WILL ALSO ACCEPT 4809 AND 8088 SERIES TERMINALS. FOR USE WITH 22-30 GAUGE WIRE WITH (.157)/.062 DIAMETER MAXIMUM WIRE INSULATION.
- LAST CIRCUIT NUMBER NOT PRESENT ON 2-6 CKT AND MAY OR MAY NOT BE PRESENT ON 7-16 CKT SIZES.
- CIRCUIT NUMBER "1" AND ENGINEERING NUMBER TO APPEAR ON PARTS 3 CKTS. AND HIGHER.
- THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

NO. OF CKT'S.	DIM. A	DIM. B
2	(2.54+0.05) .100+0.02	(5.64) .222
3	(5.08+0.05) .200+0.02	(8.18) .322
4	(7.62+0.08) .300+0.03	(10.72) .422
5	(10.16+0.08) .400+0.03	(13.26) .522
6	(12.70+0.10) .500+0.04	(15.80) .622
7	(15.24+0.10) .600+0.04	(18.34) .722
8	(17.78+0.13) .700+0.05	(20.88) .822
9	(20.32+0.13) .800+0.05	(23.42) .922
10	(22.86+0.13) .900+0.05	(25.96) 1.022
11	(25.40+0.15) 1.000+0.06	(28.50) 1.122
12	(27.94+0.15) 1.100+0.06	(31.04) 1.222
13	(30.48+0.18) 1.200+0.07	(33.58) 1.322
14	(33.02+0.18) 1.300+0.07	(36.12) 1.422
15	(35.56+0.20) 1.400+0.08	(38.66) 1.522
16	(38.10+0.20) 1.500+0.08	(41.20) 1.622

ADD HEADER VIEW DEC NO: UCP2014-1471 DRAWN BY: DRWNK/PPER CHECKED BY: CHYKOBANDERSON APPROVED BY: APPR:FSM TH DATE: 2013/10/01 DATE: 2013/10/02 DATE: 2013/10/09	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .01 1 PLACE ± 0.25 ± --- 0 PLACE ± ± ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM/IN SCALE 6:1 DESIGN UNITS INCH THIRD ANGLE PROJECTION	TITLE (2.54)/100 HOUSING FOR KK CRIMP TYPE TERMINALS 2695 SERIES DRAWING molex	MATERIAL NO. SEE CHART DOCUMENT NO. SD-2695	SHEET NO. 1 OF 2

[illegible]