


Tous droits strictement réservés. Reproduction ou utilisation sans autorisation écrite de FCI BV.
 ④ FCI BV

All rights strictly reserved. Reproduction or use in any form without written authority from the proprietor.
 ④ FCI BV

PRODUCT NUMBER 89021-X0Y



NOTES:

1. BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
COLOR NATURAL
2. TERMINAL MATERIAL: PHOSPHOR BRONZE.
3. UNDERPLATING 1.3 μ m Ni MINIMUM IN CONTACT AREA AND 0.3 μ m MINIMUM IN IDC AREA.
4. PLATING IDC AREA 0.5-4 μ m SnPb 85-95.

PLATING IN CONTACT AREA	
PLATING CODE	THICKNESS
-10Y	0.8 μ m GOLD
-20Y	2.0 μ m GOLD
-90Y	0.8 μ m GXT.

CODE FOR IDC SIZE	WIRE SIZE
-X01	30 AWG.
-X02	26 AWG.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
ltr	ecn no	dr	date						
A	H30135	VWO	930303	linear		projection		title CableConnector	
B	H40511	RVI	940816					6mm Terminal Block	
C	H40660	RVI	941018	angles					
				dr	H v Woensel	930127		product family	METRAL (tm)
				enr	E Feijen	940816		size	dwg no
				chr	P Schalk	930127		scale	213
				appd	H v Woensel	930127		scale	5:1
sheet index	revision	C						A3	89021
	sheet	1							1 of 1