

805-0803

## 156-00591

Cable Tie and Edge Clip, 50lb, 7.9", EC20 Panel Thickness .12" -.24", PA66UV Tie, HIRHS MNT, 100/pk

Article Number: 156-00591

Part Number: 156-00591

Type: T50REC20



### Base Data

<b>Part No.</b>	156-00591
<b>Type</b>	T50REC20
<b>Color</b>	Black
<b>Features</b>	HellermannTyton's UV stabilized tie and edge clip assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
<b>Application</b>	The UV stabilized tie and edge clip assemblies are ideal for use where holes are not available or where adhesives are not strong enough. Edge clips are widely used for fixing and bundling cables and wires in the automotive, harness making, panel building and renewable energy industry.
<b>Identification Plate</b>	none
<b>Position</b>	
<b>Variant</b>	Inside Serrated

### Product Dimensions

**Min. Tensile Strength** 50 lbs / 225 N

<b>Length (L)</b>	7.9 " / 200 mm
<b>Length (L2)</b>	14.8 mm
<b>Width (W)</b>	.12 " / 4.6 mm
<b>Width (W2)</b>	14.0 mm
<b>Height (H)</b>	0.05 " / 1.2 mm
<b>Height (H2)</b>	17.8 mm
<b>Min. Ø Bundle</b>	0.04 " / 1.0 mm
<b>Max. Ø Bundle</b>	1.77 " / 45.0 mm
<b>Max. Panel Thickness</b>	.24 " / 6.00 mm

**Min. Panel Thickness** 0.12 " / 3.00 mm

#### **Material and Specifications**

---

**Material** Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) / Polyamide 6.6 UV-stabilized (PA66UV)

**Cable Tie** Polyamide 6.6 UV-stabilized (PA66UV)

**Edge Clip** Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) / Stainless Steel (SS)