






D

C

B

A




3-DIMENSIONAL MODEL
NTS

27.43	1.080
26.67	1.050
14.73	.580
11.68	.460
7.62	.300
0.38	.015
0.25	.010
0.13	.005
MM	IN
CONVERSION TABLE	


NOTES:

- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
 - SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS [.5 LBS].
 - DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- △4 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- △5 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
- △6 TRADEMARK LOCATION (AMP OR TE CONNECTIVITY).
- △7 MANUFACTURING LOCATION ID (OPTIONAL).
- △8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI







DETAIL A
OPTIONAL CONSTRUCTION

△8 OBSOLETE	BLACK	1-480702-9
	-GRAY	1-480702-8
	BLUE	1-480702-6
	GREEN	1-480702-5
	YELLOW	1-480702-4
△8 SUPERSEDED BY 1-480700-0	ORANGE	1-480702-3
△8 OBSOLETE	RED	1-480702-2
	BROWN	1-480702-1
	NATURAL	1-480702-0
	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 08FEB95	 TE Connectivity	
		CHK R. SWING 08FEB95		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± 1. PLC ± 0.13 2. PLC ± 3. PLC ± 4. PLC ± ANGLES ± 0°30'	APVD D.SELF 08FEB95	NAME	
		PRODUCT SPEC	PLUG, 4 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
	FINISH -	APPLICATION SPEC	SIZE	CAGE CODE
		WEIGHT	A1 00779	DRAWING NO
		CUSTOMER DRAWING		SCALE
				4:1
			SHEET	1 OF 2
			REV	AP3

LOC	DIST	REVISIONS				
CM	0	REV	LTR	DESCRIPTION	DATE	OWN
				SEE SHEET 1		

- NOTES:
1. STAMP NUMBERS 3.18 HIGH AT WIRE END OF HOUSING (12 POINT DAVID TYPE).
 2. CHARACTERS TO BE POSITIONED ON HOUSING TO BE READ FROM WIRE END ONLY.
 3. VIOLET, BLACK, BROWN AND BLUE COLORED BLOCKS TO BE STAMPED WITH WHITE CHARACTERS. ALL OTHER COLORED BLOCKS TO BE STAMPED WITH BLACK CHARACTERS.



6.73	.265	—	—
5.97	.235	—	—
3.18	.125	27.43	1.080
0.38	.015	26.67	1.050
0.25	.010	14.73	.580
0.13	.005	7.62	.300
MM	IN	MM	IN
CONVERSION TABLE			

NATURAL	2-480702-0
COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN: R. VESTAL 08FEB95		 TE Connectivity			
				CHK: R. SWING 08FEB95					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV: D. SELF 08FEB95		NAME		PLUG, 4 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
		0 PLC ±		PRODUCT SPEC		SIZE: A1 CAGE CODE: 00779 DRAWING NO: 480702 RESTRICTED TO: —			
		1 PLC ±							
		2 PLC ± 0.13							
		3 PLC ±							
4 PLC ±		APPLICATION SPEC		WEIGHT					
ANGLES		FINISH		—					
MATERIAL: NYLON, UL 94V-2									