








THE PUSH BUTTON POSITION

PIN NUMBER	DIM. L(PIN LENGTH)
25,26	3.50
ALL OTHER PINS	4.25
1, 13, 38, 50	5.00

mot'l. code		tolerances unless otherwise specified		CUSTOMER COPY		title	
lfr	ecn no	dr	date	linear	projection	product family	code
A	T05-0258	A.C.	11/21/05	.XX ± 0.20	MM	CF ASS'Y, ABOVE MOUNT, LEFT PUSH, S/O=0	TWN
B	T06-0038	A.C.	3/02/06	.XX ± 0.10	MM	CF	1 of 4
C	T08-1173	S.LIN	10/12/08	0° ± 2°	MM	10061861	1 of 4
sheet index	revision	1	2	3	scale	product family	code
					NA	CF	TWN
						10061861	1 of 4



www.fciconnect.com



Recommended PCB Pattern


mat'l. code			tolerances unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	.X ± 0.30		projection		title	
A	T05-0258	A.C.	11/21/05	.XX ± 0.20				CF ASS'Y, ABOVE MOUNT, LEFT PUSH, S/O=0	
B	T06-0038	A.C.	3/02/06	.XXX ± 0.10					
C	T08-1173	S.LIN	10/12/08	0° ±2°					
				dr	ALLEN CHANG	11/03/05	product family		CF
				eng	ALLEN CHANG	11/03/05	size		dwg no
				chr	STERLING LIN	11/03/05	scale		
				qppd	H.C LIU	11/03/05	NA		A4
sheet	revision	C	C	C					
index	sheet	1	2	3					

NOTES :

1. THIS IS THE ASSEMBLY TYPE WHICH INCLUDES HEADER 10053867-E0501 AND EJECTOR 10053870-0150LF.
2. MATERIAL :
- INSULATOR : HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING: UL94V-0
COLOR: IVORY
- CONTACT : COPPER ALLOY
GROUND MOUNTING EAR: COPPER ALLOY
COVER: STAINLESS STEEL.
ARM: STAINLESS STEEL.
PUSH ROD : HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING: UL94V-0
COLOR: BLACK.
- RIVET : COPPER ALLOY
3. PLATING :
- CONTACT AREA: SELECTIVE GOLD (SEE P/N DESCRIPTION)
UNDER PLATING: 50u" NICKEL OVERALL
SOLDER TAIL AREA: 100u" TIN/LEAD OR 100u" MATTE TIN
GROUND MOUNT EAR AREA: 100u" TIN/LEAD OR 100u" MATTE TIN
4. SOLDER TAILS TO BE WITHIN 0.05 UPWARD AND 0.2 DOWNWARD FROM Z-DATUM PLACE, AND COPLANARITY OF SOLDER TAILS TO BE WITHIN 0.10mm.
5. PRODUCT SPEC: GS-12-240.
6. PACKAGING SPEC: GS-14-1040.

7. Part Number Description:

P/N: 10061861-X050 X 1 X



8. THIS PRODUCT (10061861-XXXXXXLF) MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008.
9. THIS PRODUCT (10061861-XXXXXX) MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008 EXCEPT FOR Pb.
10. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, IR OR VAPER PHASE REFLOW OVEN.
11. THE PRODUCTS WHERE THE PART NUMBER ENDS IN "LF" MEET THE CRITERIA SHOWN IN THE NOTES 8 AND 10.

mot'l. code			tolerances unless otherwise specified			CUSTOMER COPY		FCI	
litr	ecn no	dr	date	linear	angles	projection	scale	title	www.fciconnect.com
A	105-0258	A.C.	11/21/05	.XX ± 0.20		⌀	MM	CF ASS'Y, ABOVE MOUNT, LEFT PUSH, S/O=0	
B	106-0038	A.C.	3/02/06	.XXX ± 0.10		eng/ALLEN CHANG	11/03/05		
C	108-1173	S.LIN	10/12/08	0° ± 2°		dr ALLEN CHANG	11/03/05		
						eng/ALLEN CHANG	11/03/05		
						chr STERLING LIN	11/03/05		
						oppl H.C LIU	11/03/05		
sheet index	revision	C	C	C			NA	A4	10061861
sheet	sheet	1	2	3					



