



## FEMALE END VIEW



1 = BROWN  
3 = BLUE  
4 = BLACK

## MALE END VIEW




1 = BROWN  
2 = N/C  
3 = BLUE  
4 = BLACK

**Pico**  
**fast.**

**Euro**  
**fast.**

## SPECIFICATIONS

CONTACT CARRIER MATERIAL	NYLON OR TPU
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	125 VAC/VDC
OUTER JACKET MATERIAL/COLOR	TPU/BLACK
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	3x24 AWG
TEMPERATURE RANGE	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67



CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

## NOTES:

- \*\* INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- "/S90" DESIGNATES THERMOPLASTIC POLYURETHANE (TPU) CABLE.

## RELATED DOCUMENTS

1.  
2.  
3.  
4.

## 3RD ANGLE PROJECTION



THIS DRAWING IS  
CONFIDENTIAL AND THE  
PROPERTY OF TURCK  
INC. USE OF THIS  
DOCUMENT WITHOUT  
WRITTEN PERMISSION IS  
PROHIBITED.

## MATERIAL

## DRFT

## CBM

## DSGN

## SCALE

## DATE

## UNIT OF MEASUREMENT

## FINISH

CONTACT TURCK  
FOR MORE  
INFORMATION

## DO NOT SCALE THIS DRAWING

## FILE: 777000278

## SHEET 1 OF 1

## SOURCE DRAWING - FOR REFERENCE ONLY

**TURCK INC**  
High Technology Sensors and Automation Controls

3000 CAMPUS DRIVE  
MINNEAPOLIS, MN 55441  
1-800-544-7769  
(763) 553-7300  
(763) 553-0708 fax  
turck.com

PKG 3M-\*\*-RS 4T/S90

IDENTIFICATION NO.

REV

H

H UPDATE CABLE OD CK 08/05/11 35981

REV DESCRIPTION BY DATE ECO NO.

BY

DATE

ECO NO.