


## Rad-hard quad LVDS driver

Datasheet - production data



### Features

- LVDS output
- CMOS input
- Enable/Disable function with high-impedance
- ANSI TIA/EIA-644 compliant
- 400 Mbps (200 MHz)
- Cold spare on all pins
- 3.3 V operating power supply
- 4.8 V absolute rating
- Output voltage: 350 mV on 100-ohm load
- Power consumption: 55 mW at 3.3 V
- Hermetic package

- Guaranteed up to 300 krad TID
- SEL immune up to 135 MeV.cm<sup>2</sup>/mg
- SET/SEU immune up to 67 MeV.cm<sup>2</sup>/mg

### Description

The RHFLVDS31A is a quad, low-voltage, differential signaling (LVDS) driver specifically designed, packaged, and qualified for use in aerospace environments in a low-power and fast point-to-point baseband data transmission standard.

Operating at 3.3 V power supply, the RHFLVDS31A operates over a controlled impedance of 100-ohm transmission media that may be printed circuit board traces, back planes or cables.

The circuit features an internal fail-safe function to ensure a known state in case of floating input. All pins have cold spare buffers to ensure they are in high impedance when  $V_{CC}$  is tied to GND.

Designed on ST's proprietary CMOS process with specific mitigation techniques, the RHFLVDS31A achieves "best in the class" for hardness to total ionisation dose and heavy ions.

The RHFLVDS31A can operate over a large temperature range of -55 °C to +125 °C and it is housed in an hermetic Ceramic Flat-16 package.

Table 1. Device summary

Reference	SMD pin	Quality level	Package	Lead finish	Mass	EPPL <sup>(1)</sup>	Temp. range
RHFLVDS31AK1	-	Engineering model	Ceramic Flat-16	Gold	0.65 g	-	-55 °C to 125 °C
RHFLVDS31AK01V	5962F98651	QML-V flight				Target	

1. EPPL = ESA preferred part list

## Contents

<b>1</b>	<b>Functional description .....</b>	<b>3</b>
<b>2</b>	<b>Pin configuration .....</b>	<b>4</b>
<b>3</b>	<b>Maximum ratings and operating conditions .....</b>	<b>5</b>
<b>4</b>	<b>Radiation .....</b>	<b>6</b>
<b>5</b>	<b>Electrical characteristics .....</b>	<b>7</b>
<b>6</b>	<b>Test circuit .....</b>	<b>9</b>
<b>7</b>	<b>Package information .....</b>	<b>11</b>
	7.1 Ceramic Flat-16 package information .....	12
<b>8</b>	<b>Ordering information .....</b>	<b>13</b>
<b>9</b>	<b>Shipping information .....</b>	<b>13</b>
<b>10</b>	<b>Revision history .....</b>	<b>14</b>

1 Functional description

Figure 1. Logic diagram and logic symbol




Table 2. Truth table

Input	Enables		Outputs	
A	G	$\overline{G}$	Y	Z
H	H	X	H	L
L	H	X	L	H
H	X	L	H	L
L	X	L	L	H
X	L	H	Z	Z
OPEN	H	X	L	H
OPEN	X	L	L	H

- Note:
- 1 The G input features an internal pull-up network. The  $\overline{G}$  input features an internal pull-down network. If they are floating the circuit is enabled.
  - 2 L = low level, H = high Level, X = irrelevant, Z = high impedance (off)

## 2 Pin configuration

Figure 2. Pin connections (top view)




Table 3. Pin description

Pin number	Symbol	Name and function
1, 7, 9, 15	1A to 4A	Driver inputs
2, 6, 10, 14	1Y to 4Y	Driver outputs
3, 5, 11, 13	1Z to 4Z	
4	G	Enable
12	$\overline{G}$	
8	GND	Ground
16	V <sub>CC</sub>	Supply voltage

### 3 Maximum ratings and operating conditions

Absolute maximum ratings are those values beyond which damage to the device may occur. Functional operation under these conditions is not implied.

**Table 4. Absolute maximum ratings**

Symbol	Parameter	Value	Unit
$V_{CC}$	Supply voltage <sup>(1)</sup>	4.8	V
$V_i$	TTL inputs (operating or cold spare)	-0.3 to +4.8	
$V_{OUT}$	LVDS outputs (operating or coldspare)	-0.3 to +4.8	
$T_{stg}$	Storage temperature range	-65 to +150	°C
$T_j$	Maximum junction temperature	+150	
$R_{thjc}$	Thermal resistance junction to case <sup>(2)</sup>	22	°C/W
ESD	HBM: Human body model – All pins except LVDS outputs – LVDS outputs vs. GND	2 8	kV
	CDM: Charge device model	500	V

1. All voltages, except differential I/O bus voltage, are with respect to the network ground terminal.
2. Short-circuits can cause excessive heating. Destructive dissipation can result from short-circuits on the amplifiers.

**Table 5. Operating conditions**

Symbol	Parameter	Min.	Typ.	Max.	Unit
$V_{CC}$	Supply voltage	3	3.3	3.6	V
$V_{IN}$	Driver DC input voltage (TTL inputs)	0		3.6	
$T_A$	Ambient temperature range	-55		+125	°C

## 4 Radiation

### Total dose (MIL-STD-883 TM 1019)

The products guaranteed in radiation within the RHA QML-V system fully comply with the MIL-STD-883 TM 1019 specification.

The RHFLVDS31A is RHA QML-V, tested and characterized in full compliance with the MIL-STD-883 specification, between 50 and 300 rad/s only (full CMOS technology).

All parameters provided in [Table 7: Electrical characteristics](#) apply to both pre- and post-irradiation, as follows:

- All test are performed in accordance with MIL-PRF-38535 and test method 1019 of MIL-STD-883 for total ionizing dose (TID).
- The initial characterization is performed in qualification only on both biased and unbiased parts.
- Each wafer lot is tested at high dose rate only, in the worst bias case condition, based on the results obtained during the initial qualification.

### Heavy ions

The behavior of the product when submitted to heavy ions is not tested in production. Heavy-ion trials are performed on qualification lots only.

**Table 6. Radiation**

Type	Characteristics	Value	Unit
TID	High-dose rate (50 - 300 rad/sec) up to:	300	krad
Heavy ions	SEL immune up to: (with a particle angle of 60 ° at 125 °C)	135	MeV.cm <sup>2</sup> /mg
	SEL immune up to: (with a particle angle of 0 ° at 125 °C)	67	
	SET/SEU immune up to: (at 25 °C)	67	

## 5 Electrical characteristics

In [Table 7](#) below,  $V_{CC} = 3\text{ V}$  to  $3.6\text{ V}$ , capa-load (CL) =  $10\text{ pF}$ , typical values are at  $T_{\text{amb}} = +25\text{ }^{\circ}\text{C}$ , min. and max values are at  $T_{\text{amb}} = -55\text{ }^{\circ}\text{C}$  and  $+125\text{ }^{\circ}\text{C}$  unless otherwise specified

**Table 7. Electrical characteristics**

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$I_{CCL}$	Total enabled supply current, drivers enabled, not switching	$V_{IN} = 0\text{ V}$ or $V_{CC}$ Load = $100\text{ }\Omega$ on all channels		16.5	20	mA
$I_{CCZ}$	Total disabled supply current, loaded or not loaded, drivers disabled	$V_{IN} = 0\text{ V}$ or $V_{CC}$ $G = \text{GND}$ , $\overline{G} = V_{CC}$		2.8	4	
$I_{OFF}^{(1)}$	TTL input power-off leakage current	$V_{CC} = 0\text{ V}$ , $V_{IN} = 3.6\text{ V}$	-10		10	$\mu\text{A}$
	LVDS output power-off leakage current	$V_{CC} = 0\text{ V}$ , $V_{OUT} = 3.6\text{ V}$	-50		+50	
$V_{OH}$	Output voltage high	$R_L = 100\text{ }\Omega$			1.65	V
$V_{OL}$	Output voltage low		0.925			
$V_{OD1}$	Differential output voltage		250		400	mV
$DV_{OD1}$	Change of magnitude of $V_{OD1}$ for complementary output states				10	
$V_{OS}$	Offset voltage		1.125		1.45	V
$DV_{OS}$	Change of magnitude of $V_{OS}$ for complementary output states				15	mV
$I_{OS}$	Output short-circuit current	$V_{IN} = 0\text{ V}$ and $V_{O(Z)} = 0\text{ V}$ or $V_{IN} = V_{CC}$ and $V_{O(Y)} = 0\text{ V}$	-9			mA
$I_O$	High impedance output current	Disabled, $V_{OUT} = 3.6\text{ V}$ or GND	-10		10	$\mu\text{A}$
$V_{IH}$	Input voltage high	$G$ , $\overline{G}$ , and TTL inputs	2		$V_{CC}$	V
$V_{IL}$	Input voltage low		GND		0.8	
$I_{IH}$	High level input current	$G$ , $\overline{G}$ , and TTL inputs $V_{CC} = 3.6\text{ V}$ , $V_{IN} = V_{CC}$	-10		10	$\mu\text{A}$
$I_{IL}$	Low level input current	$G$ , $\overline{G}$ and TTL inputs $V_{CC} = 3.6\text{ V}$ , $V_{IN} = 0$	-10		10	
$C_{IN}$	Input capacitance			3		pF

Table 7. Electrical characteristics (continued)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{PHLD}$	Propagation delay time, high to low output	Refer to <a href="#">Figure 4</a>	0.5		1.5	ns
$t_{PLHD}$	Propagation delay time, low to high output		0.5		1.5	
$t_r$	Differential output signal rise time			0.8		
$t_f$	Differential output signal fall time			0.8		
$t_{SK1}$	Channel-to-channel skew <sup>(2)</sup>	Load: refer to <a href="#">Figure 4</a>			0.28	ns
$t_{SK2}$	Chip-to-chip skew <sup>(3)(4)</sup>				0.7	
$t_{SKD}$	Differential skew <sup>(5)</sup> ( $t_{PHLD} - t_{PLHD}$ )				0.3	
$t_{PHZ}$	Propagation delay time, high level to high impedance output				2.8	
$t_{PLZ}$	Propagation delay time, low level to high impedance output				2.8	
$t_{PZH}$	Propagation delay time, high impedance to high level output				2.5	
$t_{PZL}$	Propagation delay time, high impedance to low level output				2.5	

1. All pins except pin under test and  $V_{CC}$  are floating.
2.  $t_{SK1}$  is the maximum delay time difference between all outputs of the same device (measured with all inputs connected together).
3.  $t_{SK2}$  is the maximum delay time difference between outputs of all devices when they operate with the same supply voltage, at the same temperature.
4. Guaranteed by design.
5.  $t_{SKD}$  is the maximum delay time difference between  $t_{PHLD}$  and  $t_{PLHD}$  (see [Figure 4](#)).

### Cold sparing


The RHFLVDS31A features a cold spare input and output buffer. In high reliability applications, cold sparing enables a redundant device to be tied to the data bus with its power supply at 0 V ( $V_{CC} = GND$ ) without affecting the bus signals or injecting current from the I/Os to the power supplies. Cold sparing also allows redundant devices to be kept powered off so that they can be switched on only when required. This has no impact on the application. Cold sparing is achieved by implementing a high impedance between the I/Os and  $V_{CC}$ . ESD protection is ensured through a non-conventional dedicated structure.

### Fail-safe


In many applications, inputs need a fail-safe function to avoid an uncertain output state when the inputs are not connected properly. In case of TTL floating inputs, the LVDS outputs remain in a stable logic-high state.

## 6 Test circuit

**Figure 3. Voltage and current definition**




**Figure 4. Test circuit, timing and voltage definitions for differential output signal**



1. All input pulses are supplied by a generator with the following characteristics:  $t_r$  or  $t_f \leq 1$  ns,  $f = 1$  MHz,  $Z_O = 50 \Omega$ , and duty cycle = 50%.
2. The product is guaranteed in test with  $CL = 10$  pF

Figure 5. Enable and disable waveform




1. All input pulses are supplied by a generator with the following characteristics:  $t_r$  or  $t_f \leq 1$  ns,  $f_G$  or  $f_{\overline{G}} = 500$  kHz, and pulse width G or  $\overline{G} = 500$  ns.
2. The product is guaranteed in test with CL = 10 pF

## 7 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK<sup>®</sup> packages, depending on their level of environmental compliance. ECOPACK<sup>®</sup> specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK<sup>®</sup> is an ST trademark.

## 7.1 Ceramic Flat-16 package information

Figure 6. Ceramic Flat-16 package mechanical drawing



1. The upper metallic lid is electrically connected to ground.

Table 8. Ceramic Flat-16 package mechanical data

Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	2.31		2.72	0.091		0.107
b	0.38		0.48	0.015		0.019
c	0.10		0.18	0.004		0.007
D	9.75		10.13	0.384		0.399
E	6.75		7.06	0.266		0.278
E2		4.32			0.170	
E3	0.76			0.030		
e		1.27			0.050	
L	6.35		7.36	0.250		0.290
Q	0.66		1.14	0.026		0.045
S1	0.13			0.005		

## 8 Ordering information

Table 9. Order codes

Order code	Description	Temp. range	Package	Marking <sup>(1)</sup>	Packing
RHFLVDS31AK1	Engineering model	-55 °C to 125 °C	Ceramic Flat-16	RHFLVDS31AK1	Strip pack
RHFLVDS31AK01V	QML-V flight			5962F9865107VZC	

1. Specific marking only. Complete marking includes the following:
- SMD pin (on QML-V flight only)
  - ST logo
  - Date code (date the package was sealed) in YYWWA (year, week, and lot index of week)
  - QML logo (Q or V)
  - Country of origin (FR = France).

*Note:* Contact your ST sales office for information regarding the specific conditions for products in die form and QML-Q versions.

## 9 Shipping information

### Date code

The date code is structured as follows:

- Engineering model: EM xyywwz
- QML flight model: FM yywwz

Where:

x = 3 (EM only), assembly location Rennes (France)

yy = last two digits of the year

ww = week digits

z = lot index of the week

## 10 Revision history

**Table 10. Document revision history**

Date	Revision	Changes
29-Oct-2013	1	Initial release
30-Oct-2014	2	<ul style="list-style-type: none"><li>– Updated production status and marking information relative to order code RHFLVDS31AK01V in Table 1: Device summary and Table 9: Order codes.</li><li>– Changed title of Section 4 to “Radiation” and moved Electrical characteristics to Section 5.</li></ul>
04-Mar-2015	3	Added $V_{OUT}$ to Table 4: Absolute maximum ratings.
28-Apr-2017	4	<a href="#">Table 1: Device summary</a> : added mass value

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics – All rights reserved