



UVC

Ultra-Miniature-Sized for adapters.




- One rank smaller case sizes than UVY.
- Suited for adapter circuit.
- Compliant to the RoHS directive (2011/65/EU).



Specifications


Item	Performance Characteristics											
Category Temperature Range	-40 to +105°C											
Rated Voltage Range	400V											
Rated Capacitance Range	4.7 to 18μF											
Capacitance Tolerance	±20% at 120Hz, 20°C											
Leakage Current	I = 0.04CV+100 (μA) or less											
Tangent of loss angle (tan δ)	<table><tr><td>Rated voltage (V)</td><td>400</td></tr><tr><td>tan δ (MAX.)</td><td>0.25</td></tr></table>	Rated voltage (V)	400	tan δ (MAX.)	0.25	Measurement frequency : 120Hz, at 20°C						
Rated voltage (V)	400											
tan δ (MAX.)	0.25											
Stability at Low Temperature	<table><tr><td colspan="2">Rated voltage (V)</td><td>400</td></tr><tr><td>Impedance ratio</td><td>Z-25°C / Z+20°C</td><td>6</td></tr><tr><td>ZT / Z20 (MAX.)</td><td>Z-40°C / Z+20°C</td><td>10</td></tr></table>	Rated voltage (V)		400	Impedance ratio	Z-25°C / Z+20°C	6	ZT / Z20 (MAX.)	Z-40°C / Z+20°C	10	Measurement frequency : 120Hz	
Rated voltage (V)		400										
Impedance ratio	Z-25°C / Z+20°C	6										
ZT / Z20 (MAX.)	Z-40°C / Z+20°C	10										
Endurance	<div>The specifications listed at right shall be met when the capacitors are restored to 20°C after D.C. bias plus rated ripple current is applied for 2000 hours at 105°C, the peak voltage shall not exceed the rated voltage.</div> <table><tr><td>Capacitance change</td><td>Within ±25% of the initial capacitance value</td></tr><tr><td>tan δ</td><td>200% or less than the initial specified value</td></tr><tr><td>Leakage current</td><td>Less than or equal to the initial specified value</td></tr></table>			Capacitance change	Within ±25% of the initial capacitance value	tan δ	200% or less than the initial specified value	Leakage current	Less than or equal to the initial specified value			
Capacitance change	Within ±25% of the initial capacitance value											
tan δ	200% or less than the initial specified value											
Leakage current	Less than or equal to the initial specified value											
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.											
Marking	Printed with white color letter on dark brown sleeve.											

Radial Lead Type



•Please refer to page 20 about the end seal configuration.

Type numbering system (Example : 400V 15µF)



※ Configuration

ϕD	Pb-free leadwire Pb-free PET sleeve
8 · 10	PD

Dimensions

V		400	
Cap.(µF)	Code	2G	
4.7	4R7	8 × 11.5	70
5.6	5R6	8 × 11.5	70
8.2	8R2	8 × 16	85
10	100	10 × 12.5	100
12	120	8 × 20	120
15	150	10 × 16	150
18	180	10 × 20	200
		Case size $\phi D \times L$ (mm)	Rated ripple

Rated ripple current (mA rms) at 105°C 120Hz

Please refer to page 20, 21, 22 about the formed or taped product spec.
Please refer to page 4 for the minimum order quantity.

Frequency coefficient of rated ripple current

Cap.(µF)	Frequency	50Hz	120Hz	500Hz	1 kHz	10kHz or more
4.7 to 8.2		0.65	1.00	1.20	1.30	1.50
10 to 18		0.80	1.00	1.20	1.30	1.50