

Thermofit[®] Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 209A300
Description : Hex Boot

NOTES

- 1. All dimensions are in inches.
- 2. Dimensions appearing in table are as follows:
a - As Supplied




TABLE OF DIMENSIONS								
PART NUMBER	H Max a	J Min a	K Max a	P Ref a	R + .30 - .10 a	S ± .30 a	JO ± .10 a	W ± .030 a
209A300	1.66	.375	1.44	5.00	3.50	4.00	1.00	.125

Raychem
RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : A
Date : 2/10/99

Part Number : 209A300
Description : Hex Boot

Thermofit[®] Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 209A300
Description : Hex Boot

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-102	SRA	RT-1178			

ORDERING INFORMATION

209A300

-102

-XX

/XXX

Base part number

Material dash number
(See Compatability Chart)

Modification number
(If necessary, see front of scd binder for a complete list)

Adhesive slash number
(If necessary, see Compatability Chart)

OBSOLETE
NOT the LATEST
REVISION

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

If this document is printed it becomes uncontrolled. Check for the latest revision.

Raychem
RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : A
Date : 2/10/99

Part Number : 209A300
Description : Hex Boot