



Aluminum electrolytic capacitors

Capacitors with screw terminals

Series/Type: B43464, B43484

Date: February 2014

Capacitors with screw terminals**B43464, B43484****Standard – 85 °C****General-purpose grade capacitors****Applications**



- Uninterruptible power supplies
- Frequency converters

Features

- All-welded construction ensures reliable electrical contact
- RoHS-compatible


Construction

- Charge-discharge proof, polar
- Aluminum case with insulating sleeve
- Poles with screw terminal connections
- Mounting with ring clips, clamps or threaded stud
- The bases of types with threaded stud and $d \leq 76.9$ mm are not insulated



B43464

B43484


Specifications and characteristics in brief


Rated voltage V_R	350 ... 450 V DC		
Surge voltage V_S	$1.10 \cdot V_R$		
Rated capacitance C_R	1000 ... 12000 μF		
Capacitance tolerance	$\pm 20\% \triangleq M$		
Dissipation factor $\tan \delta$ (20 °C, 120 Hz)	≤ 0.20		
Leakage current I_{leak} (20 °C, 5 min)	$I_{\text{leak}} \leq 0.026 \mu\text{A} \cdot \left(\frac{C_R}{\mu\text{F}} \cdot \frac{V_R}{V} \right)^{0.85} + 20 \mu\text{A}$		
Self-inductance ESL	$d = 51.6 \text{ mm: approx. } 15 \text{ nH}$ $d \geq 64.3 \text{ mm: approx. } 20 \text{ nH}$		
Useful life ¹⁾ 85 °C; V_R ; $I_{AC,R}$	> 5000 h	Requirements: $ \Delta C/C \leq 15\%$ of initial value	
40 °C; V_R ; $1.5 \cdot I_{AC,R}$	> 90000 h	$\tan \delta \leq 1.75$ times initial specified limit	
Voltage endurance test 85 °C; V_R	2000 h	Requirements: $ \Delta C/C \leq 10\%$ of initial value	
		$\tan \delta \leq 1.3$ times initial specified limit	
Vibration resistance test		$I_{\text{leak}} \leq$ initial specified limit	
		To IEC 60068-2-6, test Fc: Frequency range 10 ... 55 Hz, displacement amplitude 0.75 mm, acceleration max. 10 g, duration 3×2 h. Capacitor mounted by its body which is rigidly clamped to the work surface.	
Characteristics at low temperature	Max. impedance ratio at 100 Hz	V_R	350 ... 450 V
		$Z_{-25^\circ\text{C}} / Z_{20^\circ\text{C}}$	3
		$Z_{-40^\circ\text{C}} / Z_{20^\circ\text{C}}$	10
IEC climatic category	To IEC 60068-1: 40/085/56 (-40 °C/+85 °C/56 days damp heat test)		
Detail specification Sectional specification	Similar to CECC 30301-810 IEC 60384-4		

Ripple current capability


Due to the ripple current capability of the contact elements, the following current upper limits must not be exceeded:

Capacitor diameter	51.6 mm	64.3 mm	76.9 mm
$I_{AC,\text{max}}$	30 A	40 A	50 A

1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.


B43464, B43484
Standard – 85 °C
Dimensional drawings
B43464

Ring clip/clamp mounting




Min. reach of screw = 9.5 mm

Positive pole marking: +

B43484

Threaded stud mounting




KAL1320-M-E

For types with threaded stud and $d \leq 76$ mm the base is not insulated. Also refer to the mounting instructions in chapter "Capacitors with screw terminals – Accessories".

Dimensions and weights


Ter- minal	Dimensions (mm) with insulating sleeve							Approx. weight (g)
d	$l \pm 1$	$l_1 \pm 1$	$l_2 +0/-1$	d_1	d_2 max.	$a +0.2/-0.4$		
M5	51.6 +0/-0.8	80.7	87.2	17	M12	10.2	22.2	220
M5	51.6 +0/-0.8	105.7	112.2	17	M12	10.2	22.2	280
M5	51.6 +0/-0.8	130.7	137.2	17	M12	10.2	22.2	350
M5	64.3 +0/-0.8	80.7	87.2	17	M12	13.2	28.5	370
M5	64.3 +0/-0.8	105.7	112.2	17	M12	13.2	28.5	440
M5	64.3 +0/-0.8	118.2	124.7	17	M12	13.2	28.5	510
M5	64.3 +0/-0.8	130.7	137.2	17	M12	13.2	28.5	600
M5	76.9 +0/-0.7	105.7	112.2	17	M12	13.2	31.7	620
M5	76.9 +0/-0.7	118.2	124.7	17	M12	13.2	31.7	700
M5	76.9 +0/-0.7	143.2	149.7	17	M12	13.2	31.7	840
M5	76.9 +0/-0.7	168.7	175.2	17	M12	13.2	31.7	1000
M5	76.9+0/-0.7	190.7	197.2	17	M12	13.2	31.7	1150
M5	76.9 +0/-0.7	220.7	227.2	17	M12	13.2	31.7	1300

**Packing**

Capacitor diameter d (mm)	length l (mm)	Packing units (pcs.)
51.6	all	36
64.3	all	25
76.9	105.7 - 168.7	16
	190.7 - 220.7	12



For ecological reasons the packing is pure cardboard.


B43464, B43484
Standard – 85 °C


Accessories

The following items are included in the delivery package, but are not fastened to the capacitors:

	Thread	Toothed washers	Screws/nuts	Maximum torque
For terminals	M5	A 5.1 DIN 6797	DIN 7985 / ISO 7045-M5 × 10-5.6-Z	2.5 Nm thread depth $t \geq 8 \text{ mm}$
For mounting	M12	J 12.5 DIN 6797	Hex nut BM 12 DIN 439	10 Nm

The following items must be ordered separately. For details, refer to chapter "Screw terminals – Accessories".


Item	Type
Ring clips	B44030
Clamps for capacitors with $d \geq 64.3 \text{ mm}$	B44030
Insulating parts	B44020


Overview of available types

V_R (V DC)	350	400	450
Case dimensions d × l (mm)			
C_R (μ F)			
1000		51.6 × 80.7	51.6 × 80.7
1500	51.6 × 80.7	51.6 × 80.7	51.6 × 105.7
2200	51.6 × 105.7 64.3 × 80.7	51.6 × 105.7 64.3 × 80.7	64.3 × 105.7
2700	64.3 × 80.7	51.6 × 130.7	64.3 × 105.7
3300	64.3 × 105.7	64.3 × 105.7	76.9 × 105.7
3900	64.3 × 105.7	64.3 × 118.2	64.3 × 130.7
4700	64.3 × 118.2	64.3 × 130.7 76.9 × 105.7	76.9 × 118.2
5600	76.9 × 105.7	76.9 × 118.2	76.9 × 143.2
6800	76.9 × 118.2	76.9 × 143.2	76.9 × 168.7
8200	76.9 × 143.2	76.9 × 168.7	76.9 × 220.7
10000	76.9 × 168.7	76.9 × 190.7	76.9 × 220.7
12000	76.9 × 190.7	76.9 × 220.7	

The capacitance and voltage ratings listed above are available in different cases upon request.

Other voltage and capacitance ratings are also available upon request.


B43464, B43484
Standard – 85 °C
Technical data and ordering codes


C_R 100 Hz 20 °C μF	Case dimensions d × l mm	ESR_{typ} 100 Hz 20 °C mΩ	Z_{max} 10 kHz 20 °C mΩ	$I_{AC,max}$ 100 Hz 40 °C A	$I_{AC,R}$ 100 Hz 85 °C A	Ordering code (composition see below)
$V_R = 350$ V DC						
1500	51.6 × 80.7	85	106	15	5.5	B434*4A4158M000
2200	51.6 × 105.7	57	71	20	7.3	B434*4A4228M000
2200	64.3 × 80.7	57	71	20	7.3	B434*4B4228M000
2700	64.3 × 80.7	45	56	23	8.5	B434*4A4278M000
3300	64.3 × 105.7	37	46	27	9.8	B434*4A4338M000
3900	64.3 × 105.7	32	40	30	10.9	B434*4A4398M000
4700	64.3 × 118.2	28	35	33	12.2	B434*4A4478M000
5600	76.9 × 105.7	25	31	37	13.4	B434*4A4568M000
6800	76.9 × 118.2	20	25	43	15.7	B434*4A4688M000
8200	76.9 × 143.2	16	20	50	18.4	B434*4A4828M000
10000	76.9 × 168.7	12	15	50	22.4	B434*4A4109M000
12000	76.9 × 190.7	10	13	50	26.1	B434*4A4129M000
$V_R = 400$ V DC						
1000	51.6 × 80.7	100	125	13	4.8	B434*4A9108M000
1500	51.6 × 80.7	74	93	16	6.0	B434*4A9158M000
2200	51.6 × 105.7	55	69	21	7.7	B434*4A9228M000
2200	64.3 × 80.7	55	56	21	7.5	B434*4B9228M000
2700	51.6 × 130.7	45	56	25	9.0	B434*4A9278M000
3300	64.3 × 105.7	37	46	28	10.1	B434*4A9338M000
3900	64.3 × 118.2	31	39	32	11.5	B434*4A9398M000
4700	64.3 × 130.7	25	31	37	13.5	B434*4A9478M000
4700	76.9 × 105.7	25	31	36	13.3	B434*4B9478M000
5600	76.9 × 118.2	22	28	40	14.8	B434*4A9568M000
6800	76.9 × 143.2	18	23	47	17.2	B434*4A9688M000
8200	76.9 × 168.7	15	19	50	19.9	B434*4A9828M000
10000	76.9 × 190.7	12	15	50	23.8	B434*4A9109M000
12000	76.9 × 220.7	10	13	50	27.8	B434*4A9129M000

Composition of ordering code

* = Mounting style

6 = for capacitors with ring clip/clamp mounting

8 = for capacitors with threaded stud


Technical data and ordering codes


C_R 100 Hz 20 °C μF	Case dimensions d × l mm	ESR _{typ} 100 Hz 20 °C mΩ	Z _{max} 10 kHz 20 °C mΩ	I _{AC,max} 100 Hz 40 °C A	I _{AC,R} 100 Hz 85 °C A	Ordering code (composition see below)
$V_R = 450 \text{ V DC}$						
1000	51.6 × 80.7	110	138	13	4.7	B434*4A5108M000
1500	51.6 × 105.7	72	90	17	6.4	B434*4A5158M000
2200	64.3 × 105.7	50	63	23	8.2	B434*4A5228M000
2700	64.3 × 105.7	44	55	25	9.1	B434*4A5278M000
3300	76.9 × 105.7	35	44	30	10.8	B434*4A5338M000
3900	64.3 × 130.7	30	38	33	12.2	B434*4A5398M000
4700	76.9 × 118.2	23	29	39	14.4	B434*4A5478M000
5600	76.9 × 143.2	20	25	44	16.2	B434*4A5568M000
6800	76.9 × 168.7	17	21	50	18.5	B434*4A5688M000
8200	76.9 × 220.7	14	18	50	21.7	B434*4A5828M000
10000	76.9 × 220.7	12	15	50	24.9	B434*4A5109M000



Composition of ordering code

* = Mounting style

6 = for capacitors with ring clip/clamp mounting

8 = for capacitors with threaded stud


B43464, B43484
Standard – 85 °C
Useful life¹⁾


 depending on ambient temperature T_A under ripple current operating conditions

Frequency factor of permissible ripple current I_{AC} versus frequency f


1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.




Frequency characteristics of ESR


Typical behavior



Impedance Z versus frequency f

Typical behavior at 20 °C



**B43464, B43484****Standard – 85 °C**

Cautions and warnings

Personal safety

The electrolytes used by EPCOS have been optimized both with a view to the intended application and with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC).

Furthermore, some of the high-voltage electrolytes used by EPCOS are self-extinguishing.


As far as possible, EPCOS does not use any dangerous chemicals or compounds to produce operating electrolytes. However, in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no alternative materials are currently known. However, the amount of dangerous materials used in our products is limited to an absolute minimum.

Materials and chemicals used in EPCOS aluminum electrolytic capacitors are continuously adapted in compliance with the EPCOS Corporate Environmental Policy and the latest EU regulations and guidelines such as RoHS, REACH/SVHC, GADSL, and ELV.

MDS (Material Data Sheets) are available on the EPCOS website for all types listed in the data book. MDS for customer specific capacitors are available upon request.

MSDS (Material Safety Data Sheets) are available for all of our electrolytes upon request.


Nevertheless, the following rules should be observed when handling aluminum electrolytic capacitors: No electrolyte should come into contact with eyes or skin. If electrolyte does come into contact with the skin, wash the affected areas immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment. Avoid inhaling electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.




Product safety

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of chapter "General technical information".

Topic	Safety information	Reference chapter "General technical information"
Polarity	Make sure that polar capacitors are connected with the right polarity.	1 "Basic construction of aluminum electrolytic capacitors"
Reverse voltage	Voltages polarity classes should be prevented by connecting a diode.	3.1.6 "Reverse voltage"
Mounting position of screw-terminal capacitors	Do not mount the capacitor with the terminals (safety vent) upside down.	11.1. "Mounting positions of capacitors with screw terminals"
Robustness of terminals	The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2.5 Nm M6: 4.0 Nm	11.3 "Mounting torques"
Mounting of single-ended capacitors	The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires. Avoid any compressive, tensile or flexural stress. Do not move the capacitor after soldering to PC board. Do not pick up the PC board by the soldered capacitor. Do not insert the capacitor on the PC board with a hole space different to the lead space specified.	11.4 "Mounting considerations for single-ended capacitors"
Soldering	Do not exceed the specified time or temperature limits during soldering.	11.5 "Soldering"
Soldering, cleaning agents	Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.	11.6 "Cleaning agents"
Upper category temperature	Do not exceed the upper category temperature.	7.2 "Maximum permissible operating temperature"
Passive flammability	Avoid external energy, such as fire or electricity.	8.1 "Passive flammability"



B43464, B43484
Standard – 85 °C

Topic	Safety information	Reference chapter "General technical information"
Active flammability	Avoid overload of the capacitors.	8.2 "Active flammability"
Maintenance	Make periodic inspections of the capacitors. Before the inspection, make sure that the power supply is turned off and carefully discharge the electricity of the capacitors. Do not apply any mechanical stress to the capacitor terminals.	10 "Maintenance"
Storage	Do not store capacitors at high temperatures or high humidity. Capacitors should be stored at +5 to +35 °C and a relative humidity of \leq 75%.	7.3 Storage conditions
Breakdown strength of insulating sleeves	Do not damage the insulating sleeve, especially when ring clips are used for mounting.	Reference chapter "Capacitors with screw terminals" "Screw terminals – accessories"



Symbols and terms

Symbol	English	German
C	Capacitance	Kapazität
C_R	Rated capacitance	Nennkapazität
C_S	Series capacitance	Serienkapazität
$C_{S,T}$	Series capacitance at temperature T	Serienkapazität bei Temperatur T
C_f	Capacitance at frequency f	Kapazität bei Frequenz f
d	Case diameter, nominal dimension	Gehäusedurchmesser, Nennmaß
d_{\max}	Maximum case diameter	Maximaler Gehäusedurchmesser
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatzserienwiderstand
ESR_f	Equivalent series resistance at frequency f	Ersatzserienwiderstand bei Frequenz f
ESR_T	Equivalent series resistance at temperature T	Ersatzserienwiderstand bei Temperatur T
f	Frequency	Frequenz
I	Current	Strom
I_{AC}	Alternating current (ripple current)	Wechselstrom
$I_{AC,rms}$	Root-mean-square value of alternating current	Wechselstrom, Effektivwert
$I_{AC,f}$	Ripple current at frequency f	Wechselstrom bei Frequenz f
$I_{AC,max}$	Maximum permissible ripple current	Maximal zulässiger Wechselstrom
$I_{AC,R}$	Rated ripple current	Nennwechselstrom
$I_{AC,R}$ (B)	Rated ripple current for base cooling	Nennwechselstromstrom für Bodenkühlung
I_{leak}	Leakage current	Reststrom
$I_{\text{leak,op}}$	Operating leakage current	Betriebsreststrom
l	Case length, nominal dimension	Gehäselänge, Nennmaß
l_{\max}	Maximum case length (without terminals and mounting stud)	Maximale Gehäselänge (ohne Anschlüsse und Gewindegöhlen)
R	Resistance	Widerstand
R_{ins}	Insulation resistance	Isolationswiderstand
R_{symm}	Balancing resistance	Symmetrierwiderstand
T	Temperature	Temperatur
ΔT	Temperature difference	Temperaturdifferenz
T_A	Ambient temperature	Umgebungstemperatur
T_C	Case temperature	Gehäsetemperatur
T_B	Capacitor base temperature	Temperatur des Becherbodens
t	Time	Zeit
Δt	Period	Zeitraum
t_b	Service life (operating hours)	Brauchbarkeitsdauer (Betriebszeit)


B43464, B43484
Standard – 85 °C

Symbol	English	German
V	Voltage	Spannung
V_F	Forming voltage	Formierspannung
V_{op}	Operating voltage	Betriebsspannung
V_R	Rated voltage, DC voltage	Nennspannung, Gleichspannung
V_s	Surge voltage	Spitzenspannung
X_C	Capacitive reactance	Kapazitiver Blindwiderstand
X_L	Inductive reactance	Induktiver Blindwiderstand
Z	Impedance	Scheinwiderstand
Z_T	Impedance at temperature T	Scheinwiderstand bei Temperatur T
$\tan \delta$	Dissipation factor	Verlustfaktor
λ	Failure rate	Ausfallrate
ϵ_0	Absolute permittivity	Elektrische Feldkonstante
ϵ_r	Relative permittivity	Dielektrizitätszahl
ω	Angular velocity; $2 \cdot \pi \cdot f$	Kreisfrequenz; $2 \cdot \pi \cdot f$

Note

All dimensions are given in mm.

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CeraLink, CeraPlas, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FilterCap, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.