

LOC
CE
DIST
16

NOT the LATEST REVISION

OB
SOLETE

Left Side

Connector(s): LC-Duplex Secure

Mode: MM

Housing Color: Slate

Geom. Spec: N/A

Fiber Path

A - _____ - B
B - _____ - A

Right Side

Connector(s): LC-Duplex


Mode: MM

Housing Color: Beige

Geom. Spec: N/A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.



Rev	Per	EC#	RELEASE	DATE	DIN	APVD
A				1/25/2008	-	JD
P	LTR		REVISION RECORD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
CHK	Jeremy Duncan		
APVD	Jeremy Duncan		
NAME	FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 1906099	1 of 4
			REV A

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	1/25/2008	-	JL	
P	LTR		REVISION RECORD	DATE	DIN	AP	

Qty	U of M	Description	Item No.
2	piece	Trace Label	7
4	piece	Eyelet/Shrink tube assembly - White	6
AR	meter	2 Fiber, XG-50/125, 2.0mm, Twinzip, Aqua, OFNR (Riser)	5
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	4
2	piece	LC Connector Assy, MM	3
2	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

DIMENSIONS: meters 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± . 4 PLC ± .		P/N Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
				CHK Jeremy Duncan		 AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
RESTRICTED TO:		APVD Jeremy Duncan		NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex					
		SCALE NTS				DRAWING NO. C- 1906099			

Restricted To:

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	1/25/2008	-	JE
P	LTR	REVISION RECORD		DATE	DIN	AP

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8 7 6 5 4 3 2 1

Label 1

Per specification 107-1645-1

XXXXXXXXXXXXXXXX

Logo

Made in XXXX

X-XXXXXXXX-X

Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1

XXXXXXXXXXXXXXXX

Logo

Made in XXXX

X-XXXXXXXX-X

Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

	A	Rev Per EC#	RELEASE	1/25/2008	-	JD			
P	LTR	REVISION RECORD		DATE	DIN	APVD			

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 P.L.C. ± - 1 P.L.C. ± - 2 P.L.C. ± - 3 P.L.C. ± - 4 P.L.C. ± -

Restricted To:

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK	Jeremy Duncan	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Jeremy Duncan			
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1906099	SHEET 4 of 4	REV A