




D

C

B

A

D

C

B

A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECO-10-012870	27APR11	HMR	DR
	G1	REVISED PER ECO-17-015223	17OCT2017	RS	DR

AMP WIRE RANGE
16-14 AWG SOLID OR STRANDED

- 1 STAMP AMP 16-14* APPROX AS SHOWN
- 2 COPPER PER ASTM B152, ANNEALED
- 3 NICKEL PLATE 0.00762(.000300)MIN EXT THK PER SAE AMS QQ-N-290
- 4 GOLD PLATE 0.00127(.000050)MIN EXT THK PER ASTM B488 TYPE 1, CODE C OVER NICKEL PLATE 0.00127[.000050] MIN EXT THK PER SAE AMS QQ-N-290 OVER Cu FLASH PER SAE AMS 2418.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm²[2,050-5,180] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

4	260°C[500°F]	1000	LOOSE PIECE	2-322694-3
3	343°C[649°F]	5000	322694 ON TAPE	2-322694-2
3	343°C[649°F]	1000	LOOSE PIECE	322694
	MAX TEMP	QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-19-93		 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 4-19-93					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DA PATTERSON 4-19-93		NAME TERMINAL, RING TONGUE HEAT RESISTANT, STRATO-THERM, 16-14 AWG		
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± ±		PRODUCT SPEC —				
	FINISH		APPLICATION SPEC —				
MATERIAL 	SEE TABLE		WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=322694	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 8:1	SHEET 1 of 1	REV G1	