

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOCAD

DIST00

F	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

9

.625	.050	1.250	1.350	27	1.530	28	9-104074-0
1.175	.050	2.350	2.450	49	2.630	50	8-104074-9
1.050	.050	2.100	2.200	44	2.380	45	8-104074-8
.925	.050	1.850	1.950	39	2.130	40	8-104074-7
.825	.050	1.650	1.750	35	1.930	36	8-104074-6
.600	.050	1.200	1.300	26	1.480	27	8-104074-5
-	.050	.950	1.050	21	1.230	22	8-104074-4
-	.050	.700	.800	16	.980	17	8-104074-3
-	.050	.500	.600	12	.780	13	8-104074-2
-	.050	.450	.550	11	.730	12	8-104074-1
-	.175	-	.350	7	.530	8	8-104074-0
-	.150	-	.300	6	.480	7	7-104074-9
-	.125	-	.250	5	.430	6	7-104074-8
-	.075	-	.150	3	.330	4	7-104074-7
.675	.050	1.350	1.450	29	1.630	30	7-104074-6
-	.050	1.100	1.200	24	1.380	25	7-104074-5
-	.050	.850	.950	19	1.130	20	7-104074-4
-	.050	.600	.700	14	.880	15	7-104074-3
-	.100	-	.200	4	.380	5	7-104074-2
-	.050	.350	.450	9	.630	10	7-104074-1

6

.625	.050	1.250	1.350	27	1.530	28	7-104074-0
1.175	.050	2.350	2.450	49	2.630	50	6-104074-9
1.050	.050	2.100	2.200	44	2.380	45	6-104074-8
.925	.050	1.850	1.950	39	2.130	40	6-104074-7
.825	.050	1.650	1.750	35	1.930	36	6-104074-6
.600	.050	1.200	1.300	26	1.480	27	6-104074-5
-	.050	.950	1.050	21	1.230	22	6-104074-4
-	.050	.700	.800	16	.980	17	6-104074-3
-	.050	.500	.600	12	.780	13	6-104074-2
-	.050	.450	.550	11	.730	12	6-104074-1
-	.175	-	.350	7	.530	8	6-104074-0
-	.150	-	.300	6	.480	7	5-104074-9
-	.125	-	.250	5	.430	6	5-104074-8
-	.075	-	.150	3	.330	4	5-104074-7
.675	.050	1.350	1.450	29	1.630	30	5-104074-6
-	.050	1.100	1.200	24	1.380	25	5-104074-5
-	.050	.850	.950	19	1.130	20	5-104074-4
-	.050	.600	.700	14	.880	15	5-104074-3
-	.100	-	.200	4	.380	5	5-104074-2
-	.050	.350	.450	9	.630	10	5-104074-1

FINISH

F

E

D

C

B

A

NO OF POSN

PART NUMBER

8

.625	.050	1.250	1.350	27	1.530	28	4-104074-0
1.175	.050	2.350	2.450	49	2.630	50	3-104074-9
1.050	.050	2.100	2.200	44	2.380	45	3-104074-8
.925	.050	1.850	1.950	39	2.130	40	3-104074-7
.825	.050	1.650	1.750	35	1.930	36	3-104074-6
.600	.050	1.200	1.300	26	1.480	27	3-104074-5
-	.050	.950	1.050	21	1.230	22	3-104074-4
-	.050	.700	.800	16	.980	17	3-104074-3
-	.050	.500	.600	12	.780	13	3-104074-2
-	.050	.450	.550	11	.730	12	3-104074-1
-	.175	-	.350	7	.530	8	3-104074-0
-	.150	-	.300	6	.480	7	2-104074-9
-	.125	-	.250	5	.430	6	2-104074-8
-	.075	-	.150	3	.330	4	2-104074-7
.675	.050	1.350	1.450	29	1.630	30	2-104074-6
-	.050	1.100	1.200	24	1.380	25	2-104074-5
-	.050	.850	.950	19	1.130	20	2-104074-4
-	.050	.600	.700	14	.880	15	2-104074-3
-	.100	-	.200	4	.380	5	2-104074-2
-	.050	.350	.450	9	.630	10	2-104074-1

1

.625	.050	1.250	1.350	27	1.530	28	2-104074-0
1.175	.050	2.350	2.450	49	2.630	50	1-104074-9
1.050	.050	2.100	2.200	44	2.380	45	1-104074-8
.925	.050	1.850	1.950	39	2.130	40	1-104074-7
.825	.050	1.650	1.750	35	1.930	36	1-104074-6
.600	.050	1.200	1.300	26	1.480	27	1-104074-5
-	.050	.950	1.050	21	1.230	22	1-104074-4
-	.050	.700	.800	16	.980	17	1-104074-3
-	.050	.500	.600	12	.780	13	1-104074-2
-	.050	.450	.550	11	.730	12	1-104074-1
-	.175	-	.350	7	.530	8	1-104074-0
-	.150	-	.300	6	.480	7	104074-9
-	.125	-	.250	5	.430	6	104074-8
-	.075	-	.150	3	.330	4	104074-7
.675	.050	1.350	1.450	29	1.630	30	104074-6
-	.050	1.100	1.200	24	1.380	25	104074-5
-	.050	.850	.950	19	1.130	20	104074-4
-	.050	.600	.700	14	.880	15	104074-3
-	.100	-	.200	4	.380	5	104074-2
-	.050	.350	.450	9	.630	10	104074-1

FINISH

F

E

D

C

B

A

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH

DWN R BROWN

CHK D SIMPSON

APVD D SIMPSON

WEIGHT -

CUSTOMER DRAWING

180CT04

180CT04

180CT04

NAME

PRODUCT SPEC

APPLICATION SPEC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

HEADER ASSEMBLY,RIGHT ANGLE

SINGLE ROW, W/SIDE & END LATCHES

AMPMODU SYSTEM 50

108-1093

114-25031

00779

104074

4:1

2

2

REV U

4805 (3/11)