


## Fiberglass Cement Resistors

# Circuit Breaker & Vertical Lead Type


## Normal Style [ FSM Series ]



### INTRODUCTION

The FSM Series Fiberglass Cement Resistors are wound on fibre glass core, have a special internal direct contact to virtually eliminate resistance changes caused by varying, often high temperatures. It offers a circuit-breaker function when overload is applied.


### DIMENSIONS




### FEATURES

|                      |                      |
|----------------------|----------------------|
| Power Rating         | 2W, 2.5W, 3.5W, 4.5W |
| Resistance Tolerance | ±5%, ±10%            |
| T.C.R.               | -80~+500ppm/°C       |


### DERATING CURVE



### TEMPERATURE RISE



Unit: mm



### STYLE

### DIMENSION

| Normal | L <sub>1</sub> | W     | H      |
|--------|----------------|-------|--------|
| FSM200 | 25±1.0         | 9±0.4 | 10±0.4 |
| FSM250 | 38±1.0         | 9±0.4 | 10±0.4 |
| FSM350 | 50±1.0         | 9±0.4 | 10±0.4 |
| FSM450 | 75±2.0         | 9±0.4 | 10±0.4 |

Note:

## ELECTRICAL CHARACTERISTICS

| STYLE                       | FSM200              | FSM250     | FSM350     | FSM450     |
|-----------------------------|---------------------|------------|------------|------------|
| Power Rating at 70°C        | 2W                  | 2.5W       | 3.5W       | 4.5W       |
| Maximum Working Voltage     | $\sqrt{P \times R}$ |            |            |            |
| Voltage Proof on Insulation | 2000V               |            |            |            |
| Resistance Range            | 0.15Ω-15KΩ          | 0.33Ω-33KΩ | 0.51Ω-47KΩ | 0.91Ω-82KΩ |
| Operating Temp. Range       | -55°C to +150°C     |            |            |            |
| Temperature Coefficient     | -80~+500ppm/°C      |            |            |            |

Note: Special value is available on request

## ENVIRONMENTAL CHARACTERISTICS

| PERFORMANCE TEST              | TEST METHOD      |                                                                  | APPRAISE                                    |
|-------------------------------|------------------|------------------------------------------------------------------|---------------------------------------------|
| Short Time Overload           | IEC 60115-1 4.13 | 10 times rated power for 5 Sec.                                  | ±2.0%+0.05Ω                                 |
| Voltage Proof on Insulation   | IEC 60115-1 4.7  | in V-block for 60 Sec., test voltage by type                     | By type                                     |
| Temperature Coefficient       | IEC 60115-1 4.8  | -55°C to +150°C                                                  | By type                                     |
| Insulation Resistance         | IEC 60115-1 4.6  | in V-block for 60 Sec.                                           | >10,000M                                    |
| Solderability                 | IEC 60115-1 4.17 | 235±5°C for 3±0.5 Sec.                                           | 95% Min. coverage                           |
| Solvent Resistance of Marking | IEC 60115-1 4.30 | IPA for 5±0.5 Min. with ultrasonic                               | "No deterioration of coatings and markings" |
| Robustness of Terminations    | IEC 60115-1 4.16 | Direct load for 10 Sec. in the direction of the terminal leads   | ≥50N                                        |
| Periodic-pulse Overload       | IEC 60115-1 4.39 | 4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)              | ±2.0%+0.05Ω                                 |
| Damp Heat Steady State        | IEC 60115-1 4.24 | 40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV        | ±2.0%+0.05Ω                                 |
| Endurance at 70°C             | IEC 60115-1 4.25 | 70±2°C at RCWV for 1,000 Hr. (1.5 Hr. on, 0.5 Hr. off)           | ±3.0%+0.05Ω                                 |
| Temperature Cycling           | IEC 60115-1 4.19 | -55°C ⇄ Room Temp. ⇄ +155°C ⇄ Room Temp. (5 cycles)              | ±2.0%+0.05Ω                                 |
| Resistance to Soldering Heat  | IEC 60115-1 4.18 | 260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body | ±0.2%+0.05Ω                                 |

Note: RCWV(Rated Continuous Working Voltage) =  $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$  or Max. working voltage listed above, whichever less.

Revision: 201304



## EXPLANATIONS OF ORDERING CODE

| MFR                                           | -12                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | F                                                                                                                                                                                                                      | T                                                                           | F                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | 52-                                                                                                                                                                                                                                                                                                   | 100R                                                                                                   |
|-----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|
| Code 1 - 3<br><b>Series Name</b><br>See Index | Code 4 - 6<br><b>Power Rating</b><br>-05 = $\varnothing$ d0.5mm<br>-06 = $\varnothing$ d0.6mm<br>-07 = $\varnothing$ d0.7mm<br>-08 = $\varnothing$ d0.8mm<br>-10 = $\varnothing$ d1.0mm<br>-14 = $\varnothing$ d1.4mm<br>-12 = 1/6W<br>-25 = 1/4W<br>25S = 1/4WS<br>-50 = 1/2W<br>50S = 1/2WS<br>100 = 1W<br>1WS = 1WS<br>200 = 2W<br>2WS = 2WS<br>204 = 0.4W<br>207 = 0.6W<br>300 = 3W<br>3WS = 3WS<br>3WM = 3WM<br>400 = 4W<br>500 = 5W<br>5WS = 5WS<br>5SS = 5WSS<br>700 = 7W<br>7WS = 7WS<br>10A = 10W<br>20A = 20W<br>30A = 30W<br>40A = 40W<br>50A = 50W<br>10S = 10WS<br>15A = 15W<br>25A = 25W<br>10B = 100W<br>25B = 250W | Code 7<br><b>Tolerance</b><br>P = $\pm 0.02\%$<br>A = $\pm 0.05\%$<br>B = $\pm 0.1\%$<br>C = $\pm 0.25\%$<br>D = $\pm 0.5\%$<br>F = $\pm 1\%$<br>G = $\pm 2\%$<br>J = $\pm 5\%$<br>K = $\pm 10\%$<br>- = Base on Spec. | Code 8<br><b>Packing Style</b><br>T = Tape/Box<br>R = Tape/Reel<br>B = Bulk | Code 9<br><b>Temperature Coefficient of Resistance</b><br>- = Base on Spec.<br>A = $\pm 5$ ppm/ $^{\circ}$ C<br>B = $\pm 10$ ppm/ $^{\circ}$ C<br>C = $\pm 15$ ppm/ $^{\circ}$ C<br>S = $\pm 20$ ppm/ $^{\circ}$ C<br>D = $\pm 25$ ppm/ $^{\circ}$ C<br>E = $\pm 50$ ppm/ $^{\circ}$ C<br>F = $\pm 100$ ppm/ $^{\circ}$ C<br>G = $\pm 200$ ppm/ $^{\circ}$ C<br>H = $\pm 250$ ppm/ $^{\circ}$ C<br>I = $\pm 300$ ppm/ $^{\circ}$ C<br>J = $\pm 350$ ppm/ $^{\circ}$ C | Code 10 - 12<br><b>Forming Type</b><br>26- = 26mm<br>52- = 52.4mm<br>73- = 73mm<br>81- = 81mm<br>91- = 91mm<br>F = F Type<br>FK = FK Type<br>FKK = FKK Type<br>FFK = F-form Kink<br>M = M-Type Forming<br>MB = M-form W/flat<br>MT = MT Type Forming<br>MR = MR Type<br>AV = AVIsert<br>PN = PANAsert | Code 13 - 17<br><b>Resistance Value</b><br>0R1 = 0.1<br>100R = 100<br>10K = 10,000<br>10M = 10,000,000 |

### EXCEPTION:

#### • Cement series:

<Code 8>: Special packing style code

B: Bulk with wirewound or metal oxide sub-assembly for resistance value

W: Bulk with ceramic based wirewound sub-assembly for resistance value

M: Bulk with metal oxide sub-assembly for resistance value

F: Bulk with Fiberglass based wirewound sub-assembly for resistance value

<Code 10-12>: Without forming code

Example: **SQP500JB-10R**

#### • JPW series:

<Code 13-17>: without resistance value code

Example: **JPW-06-T-52-**