

		DIMENSIONS IN INCHES (MILLIMETERS) DO NOT SCALE DRAWING		Dwg. No. CWR-280-XX-0000																																			
		NOTES: 1. Dimensions are in inches; dimensions in () are millimeters. 2. Metric equivalents are given for general information only, and are based upon 1.00 inches equals (25.4) millimeters. 3. Unless otherwise specified, tolerances are ±.005 (.13) for three place decimals, and ±.01 (.3) for two place decimals.																																					
		MATERIALS: PLASTIC PARTS — UL94V-0 thermoplastic (blue, standard) flame retardant. CONTACTS — Phosphor bronze. CONTACT PLATING — Selective gold plating, .000010 (Min.) in Mating Area/100 Tin Plating (Min.) in Termination Area (All Over .000050 Nickel)																																					
		OPERATING STANDARDS: TEMPERATURE RATING — 125° C CONTACT RATING — 1 ampere. DIELECTRIC STRENGTH — Over 500V.D.C. at sea level. CONDUCTORS ACCEPTED — 28-30 AWG solid or stranded. INSULATION RESISTANCE — Greater than 5 x 10 ⁹ ohms.																																					
		<table><tr><td>NO. CONTS.</td><td>A</td><td>B</td><td>C</td><td>D</td><td>E</td></tr><tr><td>9</td><td>1.224 (31.09)</td><td>.984 (24.99)</td><td>.762 (19.35)</td><td>.656 (16.66)</td><td>.434 (11.02)</td></tr><tr><td>15</td><td>1.552 (39.42)</td><td>1.312 (33.32)</td><td>1.088 (27.64)</td><td>.982 (24.94)</td><td>.760 (19.30)</td></tr><tr><td>25</td><td>2.092 (53.14)</td><td>1.852 (47.04)</td><td>1.632 (41.45)</td><td>1.526 (38.76)</td><td>1.303 (33.10)</td></tr><tr><td>37</td><td>2.740 (69.60)</td><td>2.500 (63.50)</td><td>2.284 (58.01)</td><td>2.178 (55.32)</td><td>1.955 (49.66)</td></tr></table>				NO. CONTS.	A	B	C	D	E	9	1.224 (31.09)	.984 (24.99)	.762 (19.35)	.656 (16.66)	.434 (11.02)	15	1.552 (39.42)	1.312 (33.32)	1.088 (27.64)	.982 (24.94)	.760 (19.30)	25	2.092 (53.14)	1.852 (47.04)	1.632 (41.45)	1.526 (38.76)	1.303 (33.10)	37	2.740 (69.60)	2.500 (63.50)	2.284 (58.01)	2.178 (55.32)	1.955 (49.66)				
NO. CONTS.	A	B	C	D	E																																		
9	1.224 (31.09)	.984 (24.99)	.762 (19.35)	.656 (16.66)	.434 (11.02)																																		
15	1.552 (39.42)	1.312 (33.32)	1.088 (27.64)	.982 (24.94)	.760 (19.30)																																		
25	2.092 (53.14)	1.852 (47.04)	1.632 (41.45)	1.526 (38.76)	1.303 (33.10)																																		
37	2.740 (69.60)	2.500 (63.50)	2.284 (58.01)	2.178 (55.32)	1.955 (49.66)																																		
		CUSTOMER DRAWING																																					
		<table><tr><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td><td>8</td><td>9</td><td>10</td></tr></table>				1	2	3	4	5	6	7	8	9	10																								
1	2	3	4	5	6	7	8	9	10																														
<table><tr><td>FORM-B4</td><td>REVISIONS</td></tr><tr><td>RELEASED: 11-06-2000 DWG 11-06-2000 13 2000</td><td>1 TIN-LEAD WAS REMOVED & TIN-PLATING WAS ADDED IN CONTACT PLATING. DWG 3-31-2006 G&G APR 08 2008</td></tr></table>		FORM-B4	REVISIONS	RELEASED: 11-06-2000 DWG 11-06-2000 13 2000	1 TIN-LEAD WAS REMOVED & TIN-PLATING WAS ADDED IN CONTACT PLATING. DWG 3-31-2006 G&G APR 08 2008	<table><tr><td colspan="2">ATTENTION THIS DRAWING AND ITS ATTACHMENTS, IF ANY, ARE PROPRIETARY TO CW INDUSTRIES AND DESCRIBE DESIGNS THAT ARE CONFIDENTIAL AND MUST NOT BE DISCLOSED UNLESS AUTHORIZED, IN WRITING, BY AN OFFICER OF CW INDUSTRIES.....</td><td colspan="2"><table><tr><td colspan="2">CW INDUSTRIES Southampton, Pa. 18966</td></tr><tr><td colspan="2">TOLERANCES UNLESS OTHERWISE SPECIFIED</td></tr><tr><td>2 Place Decimal ±.010</td><td>METRIC</td></tr><tr><td>3 Place Decimal ±.005</td><td>1 Place Dec. ±.25mm</td></tr><tr><td>Angles ±1°</td><td>2 Place Dec. ±.13mm</td></tr></table></td></tr><tr><td colspan="2">Made for: CW IND.</td><td colspan="2">Division: CONNECTER</td></tr><tr><td colspan="2">Drawn by: DGW 11-06-2000</td><td colspan="2">Dwg. No. CWR-280-XX-0000</td></tr><tr><td colspan="2">Checked by: G. Gold 11-13-00</td><td colspan="2"></td></tr><tr><td colspan="2">Approval: A. HOSFEU 11-13-00</td><td colspan="2"></td></tr></table>				ATTENTION THIS DRAWING AND ITS ATTACHMENTS, IF ANY, ARE PROPRIETARY TO CW INDUSTRIES AND DESCRIBE DESIGNS THAT ARE CONFIDENTIAL AND MUST NOT BE DISCLOSED UNLESS AUTHORIZED, IN WRITING, BY AN OFFICER OF CW INDUSTRIES.....		<table><tr><td colspan="2">CW INDUSTRIES Southampton, Pa. 18966</td></tr><tr><td colspan="2">TOLERANCES UNLESS OTHERWISE SPECIFIED</td></tr><tr><td>2 Place Decimal ±.010</td><td>METRIC</td></tr><tr><td>3 Place Decimal ±.005</td><td>1 Place Dec. ±.25mm</td></tr><tr><td>Angles ±1°</td><td>2 Place Dec. ±.13mm</td></tr></table>		CW INDUSTRIES Southampton, Pa. 18966		TOLERANCES UNLESS OTHERWISE SPECIFIED		2 Place Decimal ±.010	METRIC	3 Place Decimal ±.005	1 Place Dec. ±.25mm	Angles ±1°	2 Place Dec. ±.13mm	Made for: CW IND.		Division: CONNECTER		Drawn by: DGW 11-06-2000		Dwg. No. CWR-280-XX-0000		Checked by: G. Gold 11-13-00				Approval: A. HOSFEU 11-13-00			
FORM-B4	REVISIONS																																						
RELEASED: 11-06-2000 DWG 11-06-2000 13 2000	1 TIN-LEAD WAS REMOVED & TIN-PLATING WAS ADDED IN CONTACT PLATING. DWG 3-31-2006 G&G APR 08 2008																																						
ATTENTION THIS DRAWING AND ITS ATTACHMENTS, IF ANY, ARE PROPRIETARY TO CW INDUSTRIES AND DESCRIBE DESIGNS THAT ARE CONFIDENTIAL AND MUST NOT BE DISCLOSED UNLESS AUTHORIZED, IN WRITING, BY AN OFFICER OF CW INDUSTRIES.....		<table><tr><td colspan="2">CW INDUSTRIES Southampton, Pa. 18966</td></tr><tr><td colspan="2">TOLERANCES UNLESS OTHERWISE SPECIFIED</td></tr><tr><td>2 Place Decimal ±.010</td><td>METRIC</td></tr><tr><td>3 Place Decimal ±.005</td><td>1 Place Dec. ±.25mm</td></tr><tr><td>Angles ±1°</td><td>2 Place Dec. ±.13mm</td></tr></table>		CW INDUSTRIES Southampton, Pa. 18966		TOLERANCES UNLESS OTHERWISE SPECIFIED		2 Place Decimal ±.010	METRIC	3 Place Decimal ±.005	1 Place Dec. ±.25mm	Angles ±1°	2 Place Dec. ±.13mm																										
CW INDUSTRIES Southampton, Pa. 18966																																							
TOLERANCES UNLESS OTHERWISE SPECIFIED																																							
2 Place Decimal ±.010	METRIC																																						
3 Place Decimal ±.005	1 Place Dec. ±.25mm																																						
Angles ±1°	2 Place Dec. ±.13mm																																						
Made for: CW IND.		Division: CONNECTER																																					
Drawn by: DGW 11-06-2000		Dwg. No. CWR-280-XX-0000																																					
Checked by: G. Gold 11-13-00																																							
Approval: A. HOSFEU 11-13-00																																							

MASTER