




- A. Outer conductive layer (10^5 RTT)
- B. Inner non-marking neoprene layer
- C. Reinforced with 4.3 oz. polyester mesh scrim layer
- D. .060" thick, 1 1/4" wide contact area
- E. 30" long, 3/8" wide, 8 string black conductive ribbon
- F, G. 3/4", double sided hook and loop material, for quick and easy attachment to foot.

	Inner (Rust) Layer	Outside (Black) Layer	Test Method
Electrical Characteristics: Charge Decay Conductivity RTG w/1 megohm resistor RTG w/2 megohm resistor RTT Specifications: Abrasion Hardness Elongation Tensile	800 cycles 70 Shore A 600% 900lbs.	Less than 0.01 sec. 8×10^3 Ohms/sq. 1.3×10^6 Ohms max. 2.3×10^6 Ohms max. 2×10^5 Ohms max. 3000 cycles 70 Shore A 400% 2500lbs.	FTMS-1018, Method 4046 RMA-808 EOS/ESD-S4.1 @ 100V EOS/ESD-S4.1 @ 100V EOS/ESD-S4.1 @ 100V ASTM-D3389 Method B ASTM-D2240 ASTM-D412 ASTM-D412

Note:
 One heel grounder on each foot is recommended for proper grounding.
 Operator is grounded when heel is in contact with grounded dissipative or conductive flooring.
 Desco recommends the use of foot ground tester [19252](#). Ask for Technical Bulletin [TB-2040](#).
 For additional information on the use and maintenance of heel grounders please ask for Technical Bulletin [TB-2020](#).

Meets the requirements of JEDEC-108/9, MIL-HDBK-263A, MIL-STD-1686, DOD-STD-2000.

[07560](#) with 1 megohm resistor

Specifications and procedures subject to change without notice.

FOOT GROUND, HEEL, ADJUSTABLE

DESCO

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: [Desco.com](#)
 PHONE (909) 627-8178 FAX (909) 627-7449 FAX REQUEST (909) 627-7126
 DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
 PHONE (781) 821-8370 FAX (781) 575-0172

DRAWING NUMBER
 07560

DATE:
 March
 2010