

**High Performance Beta Range**


# Greentube™ SL0902 Series Gas Plasma Arresters



The Broadband Optimized™ SL0902 series has been especially developed to offer high surge ratings in a miniature package. Unique design features offer high levels of performance on fast rising transients in the domain of  $100V/\mu s$  to  $1kV/\mu s$ , which are those most likely from induced lightning disturbances.

The device offers low insertion loss, so is well suited to broadband equipment. The capacitance does not vary with voltage, so will not cause operational problems with ADSL2+ where capacitance variation across Tip and Ring is undesirable. These devices are extremely robust and are able to divert a 2500A pulse without destruction. For AC Power Cross of long duration, overcurrent protection is recommended.

## FEATURES

- RoHS compliant
- GHz working frequency
- Excellent stability on multiple pulse duty cycle
- Excellent response to fast rising transients.
- Ultra Low Insertion Loss
- Surface mountable
- 2.5KA surge capability tested with 8/20mS pulse as defined by IEC 61000-4-5

## Applications:

- Broadband equipment.
- ADSL equipment, including ADSL2+.
- XDSL equipment.
- Satellite and CATV equipment.
- General telecom equipment.



2 ELECTRODE GDT

## GRAPHICAL SYMBOL


## ORDERING INFORMATION

SL 0902 | A | XXX | SM


Type: 2 Pole Mini Arrester

Voltage:


SM=Surface mount



SL0902AxxxSM



3D T SHOWING SEATING PLANE  
FOR SL0902AxxxSM



All dimensions in mm

## Mechanical Specifications:

Weight: 0.33g (0.011 oz.)  
 Materials: Electrode Base: Copper Alloy  
 Electrode Plating: Bright Tin  
 Body: Ceramic

Device Marking: 'LF' logo, Voltage and date code  
 Packaging: Tape and Reel to EIA RS-296-D, 1500 pieces  
 Bulk in vacuum sealed bags, 1000 pieces

**High Performance Beta Range**


**Greentube™ SL0902 Series Gas Plasma Arresters**

**LITTELFUSE 2 TERMINAL MINI ARRESTER SERIES**  
**TOTALLY NON-RADIOACTIVE, UL RECOGNIZED**

Part Number	DC breakover Voltage @ 2KV/sec <sup>(1,2)</sup>	Max Dynamic Breakover Voltage @ 100V/μs (Vbr)	Max Dynamic Breakover Voltage @ 1 kV/μs (Vbr)	AC Discharge Current <sup>(4)</sup> (A)	Impulse Discharge Current <sup>(5)</sup> (KA)	Insulation Resistance <sup>(6)</sup> (Ohms)	Max Capacitance (pF)	Holdover Voltage <sup>(3)</sup> (V)	Nominal On-State Voltage @ 1A (V)
SL0902A090	72-108	300	550	2.5	2.5	1x10 <sup>9</sup>	1.5	50	20
SL0902A230	184-276	400	500	2.5	2.5	1x10 <sup>9</sup>	1.5	50	20
SL0902A350	280-420	550	650	2.5	2.5	1x10 <sup>9</sup>	1.5	50	20
SL0902A420 <sup>(7)</sup>	350-504	675	800	2.5	2.5	1x10 <sup>9</sup>	1.5	50	20

Notes:

- (1) At delivery AQL 0.65 level II, DIN ISO 2869
- (2) In ionized mode
- (3) Tested according to ITU-T Rec.K12
- (4) 10 shots, A.C. 60Hz, 1sec. duration
- (5) 10 shots, 8/20μs wave form per IEC 61000-4-5
- (6) Measured @ 100V
- (7) Pending UL approval

**Voltage vs Time Characteristic**

**Capacitance vs. Temperature @ Various Bias Voltages**
