




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	03JUN2015	DW	CW
	A1	ECR-16-013642	08MAY2017	BS	CW

D


C

B

A




PG/M THREAD-1
PG/M 螺纹孔-1



TYPE 1: SIDE ENTRY
类型1：侧出

PG/M THREAD-2
PG/M 螺纹孔-2



TYPE 2: TOP ENTRY,
OTHER SPEC. REFER TO TYPE1
类型2：顶出，其他规格参照类型1

NOTES:
1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: POWDER COATED, GREY
DEGREE OF PROTECTION: IP65 (MATED)

注释:
1. 技术参数:
主体材料: 铝合金
表面处理: 灰色粉末喷涂
防护等级: IP65(配合)

T1210240116-000	H24B-TS-PG16	H24B HOOD,SIDE ENTRY PG16,4 EAR,POWDER COATED,GREY H24B上壳,侧出PG16,4耳,灰色粉末喷涂	PG16	-	TYPE 1 类型 1
T1210240120-000	H24B-TS-M20	H24B HOOD,SIDE ENTRY M20,4 EAR,POWDER COATED,GREY H24B上壳,侧出M20,4耳,灰色粉末喷涂	M20	-	
T1210240121-000	H24B-TS-PG21	H24B HOOD,SIDE ENTRY PG21,4 EAR,POWDER COATED,GREY H24B上壳,侧出PG21,4耳,灰色粉末喷涂	PG21	-	
T1210240125-000	H24B-TS-M25	H24B HOOD,SIDE ENTRY M25,4 EAR,POWDER COATED,GREY H24B上壳,侧出M25,4耳,灰色粉末喷涂	M25	-	
T1210240132-000	H24B-TS-M32	H24B HOOD,SIDE ENTRY M32,4 EAR,POWDER COATED,GREY H24B上壳,侧出M32,4耳,灰色粉末喷涂	M32	-	TYPE 2 类型 2
T1220240116-000	H24B-TG-PG16	H24B HOOD,TOP ENTRY PG16,4 EAR,POWDER COATED,GREY H24B上壳,顶出PG16,4耳,灰色粉末喷涂	-	PG16	
T1220240121-000	H24B-TG-PG21	H24B HOOD,TOP ENTRY PG21,4 EAR,POWDER COATED,GREY H24B上壳,顶出PG21,4耳,灰色粉末喷涂	-	PG21	
T1220240125-000	H24B-TG-M25	H24B HOOD,TOP ENTRY M25,4 EAR,POWDER COATED,GREY H24B上壳,顶出M25,4耳,灰色粉末喷涂	-	M25	
T1220240129-000	H24B-TG-PG29	H24B HOOD,TOP ENTRY PG29,4 EAR,POWDER COATED,GREY H24B上壳,顶出PG29,4耳,灰色粉末喷涂	-	PG29	
T1220240132-000	H24B-TG-M32	H24B HOOD,TOP ENTRY M32,4 EAR,POWDER COATED,GREY H24B上壳,顶出M32,4耳,灰色粉末喷涂	-	M32	
T1220240140-000	H24B-TG-M40	H24B HOOD,TOP ENTRY M40,4 EAR,POWDER COATED,GREY H24B上壳,顶出M40,4耳,灰色粉末喷涂	-	M40	
T1220240134-000	H24B-TG-G3/4	H24B HOOD,TOP ENTRY G3/4,4 EAR,POWDER COATED,GREY H24B上壳,顶出G3/4,4耳,灰色粉末喷涂	-	G3/4	
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD-1 PG/M 螺纹孔-1	PG/M THREAD-2 PG/M 螺纹孔-2	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 03JUN2015 CHK Chris Wang 03JUN2015 APVD Xiang Xu 03JUN2015	TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH	NAME H24B-TS/TG-M/PG		
MATERIAL -		PRODUCT SPEC 108-137013		SIZE	RESTRICTED TO
-		APPLICATION SPEC 114-137013		CAGE CODE	
		WEIGHT -		DRAWING NO	
		Customer Drawing		SCALE 1:1	REV A1
				SHEET 1 OF 1	

D

C

B

A