

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15-92-1050](#)
Status: **Active**
Overview: [EBBI™ 50D](#)
Description: 1.27mm Pitch EBBI™ 50D Receptacle, Vertical, 50 Circuits

Documents:

[3D Model](#) [Product Specification PS-71660 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Receptacles
Series [71660](#)
Application Board-to-Board, Signal
Application Tooling Part Link [62200-4600](#)
Application Tooling Part Link [62200-5500](#)
Overview [EBBI™ 50D](#)
Product Name EBBI™
UPC 800754314916

Physical


Circuits (Loaded) 50
Circuits (maximum) 50
Color - Resin Black
Durability (mating cycles max) 2,000
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part Yes
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 2.990/g
Number of Rows 2
Orientation Vertical
PC Tail Length 3.40mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.57mm
Packaging Type Tray
Pitch - Mating Interface 1.27mm
Plating min - Mating 0.762µm
Plating min - Termination 0.254µm
Polarized to PCB Yes
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 1A
Voltage - Maximum 30V

Solder Process Data

Lead-free Process Capability SMC & Wave Capable (TH only)
Process Temperature max. C 260



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[71660Series](#)

Mates With
[71661](#)

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
IDT - Manual Press	0622004600
IDT - Manual Press	0622005500

Material Info

Old Part Number A-71660-1050

Reference - Drawing Numbers

Product Specification PS-71660
Sales Drawing SDA-71660-1***, SDA-71660-1****

This document was generated on 07/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-92-1050](#)