







SEE SHEET 2 FOR TERMINAL
TYPES AND DIMENSIONS



CIRCUIT: T TYPE UNBALANCED (SWITCH IN CENTER NEUTRAL POSITION)

SPECIFICATIONS:

MATERIAL:

BASE, PBT UL94V-0, SEE P/N TABLE

COVER, PBT UL94V-0, SEE P/N TABLE

ACTUATOR, PBT UL94V-0, WHITE

FIXED CONTACT/TERMINAL, COPPER ALLOY, PLATE-GOLD/NICKEL

MOVING CONTACT, COPPER ALLOY, PLATE-GOLD/NICKEL

ELECTRICAL:

CONTACT RATING SWITCHING, 0.4 VA @ 20V DC

INITIAL CONTACT RESISTANCE, 50 MILLIOHMS MAX.

INSULATION RESISTANCE, 100 MEGOHMS MIN. @ 100V DC.

DIELECTRIC STRENGTH, 500V AC RMS @ SEA LEVEL

LIFE, 5,000 CYCLES

MECHANICAL:

OPERATING FORCE, LESS THAN 800 GRAMS

TRAVEL, .059

ENVIRONMENTAL:

OPERATING TEMPERATURE: -30 TO +85 DEGREES C

STORAGE TEMPERATURE: -45 TO +100 DEGREES C

CLEANING, AQUEOUS OR SOLVENT

SOLDER HEAT RESISTANCE, PER 109-202, CONDITION B


SOLDERABILITY- PER JIS-C-0050 & JIS-C-00053

NOTES:

1. ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	ORANGE	3-9db $\pm$.10db	5MHz	75 Ohm	50mW	0.700	0.876	4	ATT475C04	1825284-3
	ORANGE	3-9db $\pm$.10db	5MHz	75 Ohm	50mW	0.900	1.076	5	ATT575C04	1825284-2
OBSOLETE 	BLACK	25-30db $\pm$.35db	200kHz	600 Ohm	50mW	0.900	1.076	5	ATT5600C04	1825284-1
	CASE/COVER COLOR	db RANGE TOLERANCE	FREQUENCY	IMPEDANCE	RATED POWER	DIM "M"	DIM "L"	NUMBER OF POSN.	T&B P/N	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN CMM	07AUG86	Tyco Electronics Corporation	
		CHK PS	07JUL88	Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	NAME	ATT SERIES	
	0 PLC ± —	PRODUCT SPEC	DIP SWITCH		RESTRICTED TO
	1 PLC ± —	—	—		
	2 PLC ± .01	APPLICATION SPEC	—		
	3 PLC ± —	—	SIZE	CAGE CODE	DRAWING NO
	4 PLC ± —	—	A200779		C=1825284
MATERIAL	FINISH	WEIGHT	—		—
SEE SPECIFICATION	—	CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 2
				REV	B1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	OO		—	SEE SHEET 1	—	—

D

C

B

A




D

C

B

A

1825284

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CMM 07AUG86		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
		CHK PS 07JUL88					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ATT SERIES DIP SWITCH			
	0 PLC ± -		APVD —				
	1 PLC ± -		PRODUCT SPEC —				
	2 PLC ± -		—				
	3 PLC ± .010		APPLICATION SPEC				
		4 PLC ± -		—			
MATERIAL SEE SPECIFICATION		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C=1825284	RESTRICTED TO —
		WEIGHT —		CUSTOMER DRAWING			
				SCALE 4:1	SHEET 2	OF 2	REV B1