

	1	2	3	4	5	6	7																																																																																																		
A	ON 1 2 3 4 5 6 7 8 1.80TRAVEL A 0,60±0,03 1,20±0,03 P=2,54±0,03 5,20±0,10 3,70±0,20 0,30±0,10 G Type 1,80±0,05 9,60±0,20 1,10±0,05 7,62±0,3 DRILLING PLAN L=2,54X(P-1) ∅0.8 7,62 PITCH=2,54 WIRING DIAGRAM ON 1 2 3 4 5 6 7 8 STRUCTURE: ACTUATOR COVER STATION CONTACT MOVABLE CONTACT BASE TERMINAL Specification: 1.Contact Rating Switching: 25mA 24VDC Non-switching: 100mA 50VDC 2.Contact Resistance Initial: 50m Ohms Max. After life test: 100m Ohms Max. 3.Insulation Resistance:100M Ohms Min. at 500V DC 4.Dielectric Strength: 500V AC/ 1 minute 5.Operation Force: 1000g Max. 6.Travel 1.8mm 7.Life Expectancy Mechanical Life: 5000 cycles (Min.) Electric Life: 2000 cycles /25mA 24V DC 8.Temperature Range: Operating/Storage: -40°C - +85°C Dimension A <table><tr><td>Pole</td><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td><td>8</td><td>9</td><td>10</td><td>12</td></tr><tr><td>A±0.2</td><td>3.54</td><td>6.08</td><td>8.62</td><td>11.16</td><td>13.70</td><td>16.24</td><td>18.78</td><td>21.32</td><td>23.86</td><td>26.40</td><td>31.48</td></tr></table><table><tr><td>PART</td><td>MATERIAL</td><td>FINISH</td></tr><tr><td>COVER</td><td>PBT UL 94V-0</td><td>Blue\Red</td></tr><tr><td>BASE</td><td>PA66 UL 94V-0</td><td>Black</td></tr><tr><td>ACTUATOR</td><td>PA66 UL 94V-0</td><td>White</td></tr><tr><td>STATION CONTACT</td><td>Brass</td><td>Gold Plated</td></tr><tr><td>MOVABLE CONTACT</td><td>Brass</td><td>Gold Plated</td></tr><tr><td>TERMINAL</td><td>Brass</td><td>Tin Plated</td></tr></table>							Pole	1	2	3	4	5	6	7	8	9	10	12	A±0.2	3.54	6.08	8.62	11.16	13.70	16.24	18.78	21.32	23.86	26.40	31.48	PART	MATERIAL	FINISH	COVER	PBT UL 94V-0	Blue\Red	BASE	PA66 UL 94V-0	Black	ACTUATOR	PA66 UL 94V-0	White	STATION CONTACT	Brass	Gold Plated	MOVABLE CONTACT	Brass	Gold Plated	TERMINAL	Brass	Tin Plated	A																																																				
Pole	1	2	3	4	5	6	7	8	9	10	12																																																																																														
A±0.2	3.54	6.08	8.62	11.16	13.70	16.24	18.78	21.32	23.86	26.40	31.48																																																																																														
PART	MATERIAL	FINISH																																																																																																							
COVER	PBT UL 94V-0	Blue\Red																																																																																																							
BASE	PA66 UL 94V-0	Black																																																																																																							
ACTUATOR	PA66 UL 94V-0	White																																																																																																							
STATION CONTACT	Brass	Gold Plated																																																																																																							
MOVABLE CONTACT	Brass	Gold Plated																																																																																																							
TERMINAL	Brass	Tin Plated																																																																																																							
B								B																																																																																																	
C								C																																																																																																	
D								D																																																																																																	
E								E																																																																																																	
F								F																																																																																																	
G	RoHS compliant <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td colspan="2">Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>25.01.2005</td><td>Hellwig</td><td></td></tr><tr><td>0.1~1.0</td><td>±0.05</td><td></td><td></td><td></td><td></td><td></td><td>Approved</td><td>04.03.2010</td><td>Hellwig</td><td></td></tr><tr><td>1.0~5.0</td><td>±0.1</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>5.0~10.0</td><td>±0.2</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>10~20</td><td>±0.3</td><td>②</td><td>Update</td><td>04.03.2010</td><td>Rale</td><td rowspan="3">ASSMANN WWSW/ components</td><td colspan="2">Drawing-No.</td><td colspan="2">ASSMANN WSW-No.</td></tr><tr><td>DIM</td><td>±TOL</td><td>①</td><td>Drawn</td><td>25.01.2005</td><td>Hellwig</td><td colspan="2">ASS 0190A CO</td><td colspan="2">rev02</td></tr><tr><td>X.°</td><td>±X°</td><td></td><td></td><td></td><td></td><td colspan="2">Replace</td><td colspan="2">Sheet</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td><td></td><td></td></tr></table>							Scale	1:1						Date	Name	Customer-No.		TOLERANCE							Drawn	25.01.2005	Hellwig		0.1~1.0	±0.05						Approved	04.03.2010	Hellwig		1.0~5.0	±0.1										5.0~10.0	±0.2										10~20	±0.3	②	Update	04.03.2010	Rale	ASSMANN WWSW/ components	Drawing-No.		ASSMANN WSW-No.		DIM	±TOL	①	Drawn	25.01.2005	Hellwig	ASS 0190A CO		rev02		X.°	±X°					Replace		Sheet		Angle	TOL	Id.	Modification	Date	Name						G
Scale	1:1						Date	Name	Customer-No.																																																																																																
TOLERANCE							Drawn	25.01.2005	Hellwig																																																																																																
0.1~1.0	±0.05						Approved	04.03.2010	Hellwig																																																																																																
1.0~5.0	±0.1																																																																																																								
5.0~10.0	±0.2																																																																																																								
10~20	±0.3	②	Update	04.03.2010	Rale	ASSMANN WWSW/ components	Drawing-No.		ASSMANN WSW-No.																																																																																																
DIM	±TOL	①	Drawn	25.01.2005	Hellwig		ASS 0190A CO		rev02																																																																																																
X.°	±X°						Replace		Sheet																																																																																																
Angle	TOL	Id.	Modification	Date	Name																																																																																																				
H								H																																																																																																	
	1	2	3	4	5	6	7																																																																																																		