



Amorphous Power Inductor

- ◆ For smoothing switching power supply output
- ◆ Rated Current: 30ADC
- ◆ Low core-loss at high frequency
- ◆ Amorphous iron cores with precised gap are used in the coil

Schematic Diagram;



Mechanical Specifications;



MODEL NUMBER

NAC-30 SERIES

Part Number	Rated Current (ADC)	Inductance (uH)±25%	DCR (mΩ) MAX	Wire Dia (ømm)	Dimension OD mm(In) MAX	Dimension HT mm(In) MAX
NAC-30-0011	30	10	3	1.0X6	34(1.34)	20(0.79)
NAC-30-0021	30	20	4	1.1X6	43(1.69)	21(0.83)
NAC-30-0031	30	30	4	1.1X6	44(1.73)	23(0.91)
NAC-30-0051	30	50	6	1.1X6	56(2.20)	27(1.06)
NAC-30-0101	30	100	7	1.1X6	57(2.24)	35(1.38)

PREPARED BY:

K. BRENNAN

NOTE: Inductance is measured at 20 KHz with specified DC current

ENGINEER:

M. PITCHAI

DWG CONTROL NO.
P-A4-13612
ACAD\MXFMR\A4136121.DWG

REV

-

30A POWER INDUCTOR FOR
SWITCH MODE POWER SUPPLIES

QUALITY CONTROL:

T. CLEM

CONTENTS OF THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT
PRIOR NOTICE

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(951) 699-1270 FAX 9516769482

NAC-30 SERIES

MODEL SPECIFICATION

DIM: mm(In) SCL: 1/1 SH: 1 OF 1

APPROVED:

Y. SEKIGUCHI

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tamura:

[NAC-30-0101](#)