

**TC74VHC164F, TC74VHC164FN, TC74VHC164FT****8 - BIT SHIFT REGISTER (S - IN, P - OUT)**

The TC74VHC164 is an advanced high speed CMOS 8 - BIT SERIAL - IN PARALLEL - OUT SHIFT REGISTER fabricated with silicon gate C<sup>2</sup>MOS technology.

It achieves the high speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation.

It consists of a serial - in, parallel - out 8 - bit shift register with a CLOCK input and an overriding CLEAR input.

Two serial data inputs (A, B) are provided so that one may be used as a data enable.

An input protection circuit ensures that 0 to 5.5V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5V to 3V systems and two supply systems such as battery back up. This circuit prevents device destruction due to mismatched supply and input voltages.

**FEATURES :**

- High Speed..... $f_{MAX} = 175\text{MHz}(\text{typ.})$   
at  $V_{CC} = 5\text{V}$
- Low Power Dissipation..... $I_{CC} = 4\mu\text{A}(\text{Max.})$  at  $T_a = 25^\circ\text{C}$
- High Noise Immunity..... $V_{NIH} = V_{NIL} = 28\% V_{CC} (\text{Min.})$
- Power Down Protection is provided on all inputs.
- Balanced Propagation Delays..... $t_{PLH} \approx t_{PHL}$
- Wide Operating Voltage Range....  $V_{CC} (\text{opr}) = 2\text{V} \sim 5.5\text{V}$
- Low Noise .....  $V_{OLP} = 0.8\text{V} (\text{Max.})$
- Pin and Function Compatible with 74ALS164


**TRUTH TABLE**

| INPUTS                  |                                                                                     |           |   | OUTPUTS   |                 |     |                 |
|-------------------------|-------------------------------------------------------------------------------------|-----------|---|-----------|-----------------|-----|-----------------|
| $\overline{\text{CLR}}$ | CK                                                                                  | SERIAL IN |   | QA        | QB              | ... | QH              |
|                         |                                                                                     | A         | B |           |                 |     |                 |
| L                       | X                                                                                   | X         | X | L         | L               | ... | L               |
| H                       |  | X         | X | NO CHANGE |                 |     |                 |
| H                       |  | L         | X | L         | QA <sub>n</sub> | ... | QG <sub>n</sub> |
| H                       |  | X         | L | L         | QA <sub>n</sub> | ... | QG <sub>n</sub> |
| H                       |  | H         | H | H         | QA <sub>n</sub> | ... | QG <sub>n</sub> |


X : Don't Care

QA<sub>n</sub> ~ QG<sub>n</sub>: The level of QA ~ QG, respectively, before the most recent positive edge of the clock.


(Note) The JEDEC SOP (FN) is not available in Japan.





F (SOP14-P-300-1.27)  
Weight : 0.18g (Typ.)




FN (SOL14-P-150-1.27)  
Weight : 0.12g (Typ.)




FT (TSSOP14-P-0044-0.65)  
Weight : 0.06g (Typ.)

**PIN ASSIGNMENT****IEC LOGIC SYMBOL**

SYSTEM DIAGRAM



TIMING CHART



## ABSOLUTE MAXIMUM RATINGS

| PARAMETER                   | SYMBOL    | VALUE                    | UNIT               |
|-----------------------------|-----------|--------------------------|--------------------|
| Supply Voltage Range        | $V_{CC}$  | $-0.5 \sim 7.0$          | V                  |
| DC Input Voltage            | $V_{IN}$  | $-0.5 \sim 7.0$          | V                  |
| DC Output Voltage           | $V_{OUT}$ | $-0.5 \sim V_{CC} + 0.5$ | V                  |
| Input Diode Current         | $I_{IK}$  | $-20$                    | mA                 |
| Output Diode Current        | $I_{OK}$  | $\pm 20$                 | mA                 |
| DC Output Current           | $I_{OUT}$ | $\pm 25$                 | mA                 |
| DC $V_{CC}$ /Ground Current | $I_{CC}$  | $\pm 75$                 | mA                 |
| Power Dissipation           | $P_D$     | 180                      | mW                 |
| Storage Temperature         | $T_{stg}$ | $-65 \sim 150$           | $^{\circ}\text{C}$ |

## RECOMMENDED OPERATING CONDITIONS

| PARAMETER                | SYMBOL    | VALUE                                                                             | UNIT               |
|--------------------------|-----------|-----------------------------------------------------------------------------------|--------------------|
| Supply Voltage           | $V_{CC}$  | 2.0~5.5                                                                           | V                  |
| Input Voltage            | $V_{IN}$  | 0~5.5                                                                             | V                  |
| Output Voltage           | $V_{OUT}$ | 0~ $V_{CC}$                                                                       | V                  |
| Operating Temperature    | $T_{opr}$ | $-40 \sim 85$                                                                     | $^{\circ}\text{C}$ |
| Input Rise and Fall Time | $dt/dv$   | 0~100 ( $V_{CC} = 3.3 \pm 0.3\text{V}$ )<br>0~20 ( $V_{CC} = 5 \pm 0.5\text{V}$ ) | ns/V               |

## DC ELECTRICAL CHARACTERISTICS

| PARAMETER                   | SYMBOL   | TEST CONDITION                       |                           | $V_{CC}$<br>(V)   | $T_a = 25^{\circ}\text{C}$  |                   |                             | $T_a = -40 \sim 85^{\circ}\text{C}$ |                             | UNIT          |
|-----------------------------|----------|--------------------------------------|---------------------------|-------------------|-----------------------------|-------------------|-----------------------------|-------------------------------------|-----------------------------|---------------|
|                             |          |                                      |                           |                   | MIN.                        | TYP.              | MAX.                        | MIN.                                | MAX.                        |               |
| High - Level Input Voltage  | $V_{IH}$ |                                      |                           | 2.0<br>3.0~5.5    | 1.50<br>$V_{CC} \times 0.7$ | —<br>—            | —<br>—                      | 1.50<br>$V_{CC} \times 0.7$         | —<br>—                      | V             |
| Low - Level Input Voltage   | $V_{IL}$ |                                      |                           | 2.0<br>3.0~5.5    | —<br>—                      | —<br>—            | 0.50<br>$V_{CC} \times 0.3$ | —<br>$V_{CC} \times 0.3$            | 0.50<br>$V_{CC} \times 0.3$ | V             |
| High - Level Output Voltage | $V_{OH}$ | $V_{IN} = V_{IH} \text{ or } V_{IL}$ | $I_{OH} = -50\mu\text{A}$ | 2.0<br>3.0<br>4.5 | 1.9<br>2.9<br>4.4           | 2.0<br>3.0<br>4.5 | —<br>—<br>—                 | 1.9<br>2.9<br>4.4                   | —<br>—<br>—                 | V             |
|                             |          |                                      | $I_{OH} = -4\text{mA}$    | 3.0<br>4.5        | 2.58<br>3.94                | —<br>—            | —<br>—                      | 2.48<br>3.80                        | —<br>—                      |               |
|                             |          |                                      | $I_{OH} = -8\text{mA}$    | 3.0<br>4.5        | —<br>—                      | —<br>—            | —<br>—                      | —<br>—                              | —<br>—                      |               |
| Low - Level Output Voltage  | $V_{OL}$ | $V_{IN} = V_{IH} \text{ or } V_{IL}$ | $I_{OL} = 50\mu\text{A}$  | 2.0<br>3.0<br>4.5 | —<br>—<br>—                 | 0.0<br>0.0<br>0.0 | 0.1<br>0.1<br>0.1           | —<br>—<br>—                         | 0.1<br>0.1<br>0.1           | V             |
|                             |          |                                      | $I_{OL} = 4\text{mA}$     | 3.0<br>4.5        | —<br>—                      | —<br>—            | 0.36<br>0.36                | —<br>—                              | 0.44<br>0.44                |               |
|                             |          |                                      | $I_{OL} = 8\text{mA}$     | 3.0<br>4.5        | —<br>—                      | —<br>—            | —<br>—                      | —<br>—                              | —<br>—                      |               |
| Input Leakage Current       | $I_{IN}$ | $V_{IN} = 5.5\text{V or GND}$        |                           | 0~5.5             | —                           | —                 | $\pm 0.1$                   | —                                   | $\pm 1.0$                   | $\mu\text{A}$ |
| Quiescent Supply Current    | $I_{CC}$ | $V_{IN} = V_{CC} \text{ or GND}$     |                           | 5.5               | —                           | —                 | 4.0                         | —                                   | 40.0                        |               |

TIMING REQUIREMENTS (Input  $t_r = t_f = 3\text{ns}$ )

| PARAMETER                                           | SYMBOL                   | TEST CONDITION | Ta = 25°C              |        | Ta = -40~85°C |            | UNIT |
|-----------------------------------------------------|--------------------------|----------------|------------------------|--------|---------------|------------|------|
|                                                     |                          |                | V <sub>CC</sub> (V)    | TYP .  | LIMIT         | LIMIT      |      |
| Minimum Pulse Width<br>(CK)                         | $t_{W(L)}$<br>$t_{W(H)}$ |                | 3.3 ± 0.3              | —      | 5.0           | 5.0        | ns   |
|                                                     |                          |                | 5.0 ± 0.5              | —      | 5.0           | 5.0        |      |
| Minimum Pulse Width<br>( $\overline{\text{CLR}}$ )  | $t_{W(L)}$               |                | 3.3 ± 0.3<br>5.0 ± 0.5 | —<br>— | 5.0<br>5.0    | 5.0<br>5.0 |      |
| Minimum Set - up Time                               | $t_s$                    |                | 3.3 ± 0.3<br>5.0 ± 0.5 | —<br>— | 5.0<br>4.5    | 6.0<br>4.5 |      |
| Minimum Hold Time                                   | $t_h$                    |                | 3.3 ± 0.3<br>5.0 ± 0.5 | —<br>— | 0.0<br>1.0    | 0.0<br>1.0 |      |
| Minimum Removal Time<br>( $\overline{\text{CLR}}$ ) | $t_{\text{rem}}$         |                | 3.3 ± 0.3<br>5.0 ± 0.5 | —<br>— | 2.5<br>2.5    | 2.5<br>2.5 |      |

AC ELECTRICAL CHARACTERISTICS (Input  $t_r = t_f = 3\text{ns}$ )

| PARAMETER                                               | SYMBOL                 | TEST CONDITION      |         | Ta = 25°C |      |      | Ta = -40~85°C |      | UNIT |
|---------------------------------------------------------|------------------------|---------------------|---------|-----------|------|------|---------------|------|------|
|                                                         |                        | V <sub>CC</sub> (V) | CL (pF) | MIN.      | TYP. | MAX. | MIN.          | MAX. |      |
| Propagation Delay Time<br>(CK-Q)                        | $t_{pLH}$<br>$t_{pHL}$ | 3.3 ± 0.3           | 15      | —         | 8.4  | 12.8 | 1.0           | 15.0 | ns   |
|                                                         |                        |                     | 50      | —         | 10.9 | 16.3 | 1.0           | 18.5 |      |
|                                                         |                        | 5.0 ± 0.5           | 15      | —         | 5.8  | 9.0  | 1.0           | 10.5 |      |
|                                                         |                        |                     | 50      | —         | 7.3  | 11.0 | 1.0           | 12.5 |      |
| Propagation Delay Time<br>( $\overline{\text{CLR}}$ -Q) | $t_{pHL}$              | 3.3 ± 0.3           | 15      | —         | 8.3  | 12.8 | 1.0           | 15.0 |      |
|                                                         |                        |                     | 50      | —         | 10.8 | 16.3 | 1.0           | 18.5 |      |
|                                                         |                        | 5.0 ± 0.5           | 15      | —         | 5.2  | 8.6  | 1.0           | 10.0 |      |
|                                                         |                        |                     | 50      | —         | 6.7  | 10.6 | 1.0           | 12.0 |      |
| Maximum Clock Frequency                                 | $f_{\text{MAX}}$       | 3.3 ± 0.3           | 15      | 80        | 125  | —    | 65            | —    | MHz  |
|                                                         |                        |                     | 50      | 50        | 75   | —    | 45            | —    |      |
|                                                         |                        | 5.0 ± 0.5           | 15      | 125       | 175  | —    | 105           | —    |      |
|                                                         |                        |                     | 50      | 85        | 115  | —    | 75            | —    |      |
| Input Capacitance                                       | $C_{IN}$               |                     |         | —         | 4    | 10   | —             | 10   | pF   |
| Power Dissipation Capacitance                           | $C_{PD}$               | (Note 1)            |         | —         | 76   | —    | —             | —    |      |

Note (1)  $C_{PD}$  is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.


Average operating current can be obtained by the equation :

$$I_{CC(\text{opr.})} = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC}$$

NOISE CHARACTERISTICS ( Input  $t_r = t_f = 3\text{ns}$  )


| PARAMETER                                       | SYMBOL           | TEST CONDITION        |                     | Ta = 25°C |      | UNIT |
|-------------------------------------------------|------------------|-----------------------|---------------------|-----------|------|------|
|                                                 |                  |                       | V <sub>CC</sub> (V) | TYP.      | MAX. |      |
| Quiet Output<br>Maximum Dynamic V <sub>OL</sub> | V <sub>OLP</sub> | C <sub>L</sub> = 50pF | 5.0                 | 0.5       | 0.8  | V    |
| Quiet Output<br>Minimum Dynamic V <sub>OL</sub> | V <sub>OLV</sub> | C <sub>L</sub> = 50pF | 5.0                 | −0.5      | −0.8 | V    |
| Minimum High Level<br>Dynamic Input Voltage     | V <sub>IHD</sub> | C <sub>L</sub> = 50pF | 5.0                 | —         | 3.5  | V    |
| Maximum Low Level<br>Dynamic Input Voltage      | V <sub>ILD</sub> | C <sub>L</sub> = 50pF | 5.0                 | —         | 1.5  | V    |

INPUT EQUIVALENT CIRCUIT




SOP 14PIN (200mil BODY) PACKAGE DIMENSIONS (SOP14-P-300-1.27)

Unit in mm




SOP 14PIN (150mil BODY) PACKAGE DIMENSIONS (SOP14-P-150-1.27)

Unit in mm



TSSOP 14PIN PACKAGE DIMENSIONS (TSSOP14-P-0044-0.65)

Unit in mm



**RESTRICTIONS ON PRODUCT USE**

000707EBA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.