

## Features


\* 3:1 Impedance Ratio

## Specifications @ 25°C

Frequency Range 10 - 440 MHz

Insertion Loss	Maximum
10-440 MHz	3 dB
10-320 MHz	2 dB
10-100 MHz	1 dB

## SM-22



## Schematic



## Absolute Maximum Ratings

Parameter	Absolute Maximum
RF Power	250 mW
DC Current	30 mA
Storage Temperature	-55°C to 100°C

Function	Pin No.
Primary dot	4
Primary	5
Primary CT	-
Secondary dot	3
Secondary	1
Secondary CT	-
Case Ground	-
Not Connected	2

## Additional Specifications:

Insertion Loss  
440 - 750 MHz = 4.5dB typical

Specifications Subject to Change Without Notice

S0910 D

**ADVANCED:** Data Sheets contain information regarding a product M/A-COM Technology Solutions is considering for development. Performance is based on target specifications, simulated results, and/or prototype measurements. Commitment to develop is not guaranteed.

**PRELIMINARY:** Data Sheets contain information regarding a product M/A-COM Technology Solutions has under development. Performance is based on engineering tests. Specifications are typical. Mechanical outline has been fixed. Engineering samples and/or test data may be available. Commitment to produce in volume is not guaranteed.

• North America Tel: 800.366.2266 • Europe Tel: +353.21.244.6400  
• India Tel: +91.80.4155721 • China Tel: +86.21.2407.1588

Visit [www.macomtech.com](http://www.macomtech.com) for additional data sheets and product information.

M/A-COM Technology Solutions Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[M/A-COM Technology Solutions:](#)

[ETC3-1TR](#)