




1

REELED FOR MINI APPLICATOR.

2

.000030 GOLD OVER .000050 NICKEL.

3

GOLD FLASH OVER NICKEL, .000030 GOLD ON CONTACT AREA.

4

PREPLATED:(HALT).000078-.000158 BRIGHT TIN.

5

.000050 GOLD OVER .000050 NICKEL.

6

GOLD FLASH OVER NICKEL, .000015 GOLD ON CONTACT AREA.

7

GOLD PLATING NOT REQUIRED IN THIS AREA.

8

.000050 GOLD ON CONTACT AREA, GOLD FLASH AREA L OVER.000050/.000100 NICKEL ENTIRE CONTACT.

9

SHEARED EDGES MAY BE UNPLATED.

10

REELED FOR STANDARD APPLICATOR.

11

CUT OUTS ON BOX AT MANUFACTURER'S OPTION.

12

OBSOLETE PART NUMBER.

13

PT. OF MEAS. FOR PLATING THICKNESS(INSIDE BEAMS).

14

.000015 GOLD IN THE CONTACT AREA, .000050 NICKEL OVER THE ENTIRE TERMINAL.

15

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

915

OBSOLETE

1-	12-7	87667-6	9814	1-87666-9
1-	12-1	87667-5	87	1-87666-6
1-	12-0	87667-4	67	87666-5
	12-9	87667-3	57	87666-4
	12-9	87667-3	4	87666-3
	12-8	87667-2	37	87666-2
	12-7	87667-1	27	87666-1
PART NO.		LOOSE PIECE PART NO.	FINISH	1 PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

CU-NI-SI

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	-

FINISH

SEE TABLE

APPROVALS

DWN
E.C.CLAYBAUGH

CHK
-

APVD
-

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

SCALE 8:1

SHEET 1 of 1

REV R

TE Connectivity

CONTACT, FEMALE
MOD IV, CRIMP SNAP-IN

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=87666

RESTRICTED TO
-