


# LAMINATED TRANSFORMERS

## Type EI54 / 18.8 - 16VA




Frequency 50/60Hz  
Potted under vacuum  
Split-bobbin  
Temperature class ta 40°C/B  
Weight: 0.42kg  
Packaging unit: 10 pieces (tray)

### Mechanical



### Schematics



\* Empty-Pin

| Primary (V) | Secondary (V / mA) | No-Load Voltage (V) | Schematic No. | Part Number | Agency Approvals |
|-------------|--------------------|---------------------|---------------|-------------|------------------|
| 230         | 6 / 2666           | 7.60                | 1             | 054-5187.0  | 1/3*             |
| 230         | 9 / 1777           | 11.30               | 1             | 054-5190.0  | 1/3*             |
| 230         | 12 / 1333          | 14.90               | 1             | 054-5193.0  | 1/3*             |
| 230         | 15 / 1066          | 18.40               | 1             | 054-5196.0  | 1/3*             |
| 230         | 18 / 888           | 22.40               | 1             | 054-5199.0  | 1/3*             |
| 230         | 24 / 666           | 29.60               | 1             | 054-5205.0  | 1/3*             |
| 230         | 2x6 / 1333         | 2x7.70              | 2             | 054-5210.0  | 1/3*             |
| 230         | 2x9 / 888          | 2x11.40             | 2             | 054-5213.0  | 1/3*             |
| 230         | 2x12 / 666         | 2x15.00             | 2             | 054-5216.0  | 1/3*             |
| 230         | 2x15 / 533         | 2x18.70             | 2             | 054-5219.0  | 1/3*             |
| 230         | 2x18 / 444         | 2x22.40             | 2             | 054-5222.0  | 1/3*             |
| 230         | 2x24 / 333         | 2x29.00             | 2             | 054-5228.0  | 1                |
| 115         | 6 / 2666           | 7.60                | 1             | 054-5049.0  | 1/3*             |
| 115         | 9 / 1777           | 11.30               | 1             | 054-5052.0  | 1/3*             |
| 115         | 12 / 1333          | 14.90               | 1             | 054-5055.0  | 1/3*             |
| 115         | 15 / 1066          | 18.40               | 1             | 054-5058.0  | 1/3*             |
| 115         | 18 / 888           | 22.40               | 1             | 054-5061.0  | 1/3*             |
| 115         | 24 / 666           | 29.60               | 1             | 054-5067.0  | 1/3*             |
| 115         | 2x6 / 1333         | 2x7.70              | 2             | 054-5072.0  | 1/3*             |
| 115         | 2x9 / 888          | 2x11.40             | 2             | 054-5075.0  | 1/3*             |
| 115         | 2x12 / 666         | 2x15.00             | 2             | 054-5078.0  | 1/3*             |
| 115         | 2x15 / 533         | 2x18.70             | 2             | 054-5081.0  | 1/3*             |
| 115         | 2x18 / 444         | 2x22.40             | 2             | 054-5084.0  | 1/3*             |
| 115         | 2x24 / 333         | 2x29.00             | 2             | 054-5090.0  | 1                |
| 2x115       | 6 / 2666           | 7.60                | 3             | 054-5325.0  | 1/3*             |
| 2x115       | 9 / 1777           | 11.30               | 3             | 054-5328.0  | 1/3*             |
| 2x115       | 12 / 1333          | 14.90               | 3             | 054-5331.0  | 1/3*             |
| 2x115       | 15 / 1066          | 18.40               | 3             | 054-5334.0  | 1/3*             |
| 2x115       | 18 / 888           | 22.40               | 3             | 054-5337.0  | 1/3*             |
| 2x115       | 24 / 666           | 29.60               | 3             | 054-5343.0  | 1/3*             |
| 2x115       | 2x6 / 1333         | 2x7.70              | 4             | 054-5348.0  | 1/3*             |
| 2x115       | 2x9 / 888          | 2x11.40             | 4             | 054-5351.0  | 1/3*             |
| 2x115       | 2x12 / 666         | 2x15.00             | 4             | 054-5354.0  | 1/3*             |
| 2x115       | 2x15 / 533         | 2x18.70             | 4             | 054-5357.0  | 1/3*             |
| 2x115       | 2x18 / 444         | 2x22.40             | 4             | 054-5360.0  | 1/3*             |
| 2x115       | 2x24 / 333         | 2x29.00             | 4             | 054-5366.0  | 1                |

# LAMINATED TRANSFORMERS

## Type EI54 / 18.8 - 16VA



| Primary (V) | Secondary (V / mA) | No-Load Voltage (V) | Schematic No. | Part Number | Agency Approvals |
|-------------|--------------------|---------------------|---------------|-------------|------------------|
| 230         | 6 / 2666           | 7.60                | 1             | 054-5381.0  | 1/3*             |
| 230         | 9 / 1777           | 11.30               | 1             | 054-5382.0  | 1/3*             |
| 230         | 12 / 1333          | 14.90               | 1             | 054-5383.0  | 1/3*             |
| 230         | 15 / 1066          | 18.40               | 1             | 054-5384.0  | 1/3*             |
| 230         | 18 / 888           | 22.40               | 1             | 054-5385.0  | 1/3*             |
| 230         | 24 / 666           | 29.60               | 1             | 054-5386.0  | 1/3*             |
| 230         | 2x6 / 1333         | 2x7.70              | 2             | 054-5387.0  | 1/3*             |
| 230         | 2x9 / 888          | 2x11.40             | 2             | 054-5388.0  | 1/3*             |
| 230         | 2x12 / 666         | 2x15.00             | 2             | 054-5389.0  | 1/3*             |
| 230         | 2x15 / 533         | 2x18.70             | 2             | 054-5390.0  | 1/3*             |

Frequency 50/60Hz

Potted under vacuum


Split-bobbin

Temperature class ta 40°C/B

Weight: 0.43kg

Packaging unit: 10 pieces (tray)

### Mechanical



### Schematics

