

4






3

2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC U	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	—	—	—	—



NOTES:
1. WIRE RANGE
CONDUCTOR: 0.75mm² - 2.5mm²
INSULATION DIAMETER: 2.3mm - 3.9mm

REEL	BRASS PRE-TIN	RECEPTACLE H3374ET/R8000	1-1627215-4
REEL	BRASS	RECEPTACLE H3374/R8000	1-1627215-3
LP	BRASS	RECEPTACLE H3374/10000	1-1627215-2
LP	BRASS	RECEPTACLE H3374/1000	1-1627215-1
LP	BRASS	RECEPTACLE H3374/100	1-1627215-0
REMARKS	MATERIAL	DESCRIPTION	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: W.RIEDE 2.12.04		tyco Tyco Electronics Corporation Electronics AUSTRALIA				
		CHK: H.THA1 2.12.04						
		APVD: W.RIEDE 2.12.04						
ALL DIMENSIONS IN mm:	TOLERANCES UNLESS OTHERWISE SPECIFIED: DIMENSION (mm) TOLERANCE(+/-mm)		NAME:		RECEPTACLE			
	LESS THAN 10 0.4		PRODUCT SPEC:					
	OVER 10 TO 30 0.5		-					
	OVER 30 TO 80 0.7		APPLICATION SPEC:					
	OVER 80 TO 250 1.0		-					
ANGLES ±2°		WEIGHT: -		SIZE A3	CAGE CODE	DRAWING NO C= 1627215	RESTRICTED TO -	
MATERIAL -	FINISH -		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV 0	



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA, USA.