

CentralTM

Semiconductor Corp.

145 Adams Ave., Hauppauge, NY 11788 USA
 Phone (631) 435-1110 FAX (631) 435-1824
 Manufacturer of World Class Discrete Semiconductors
www.centralsemi.com

2N2411
 2N2412

PNP SILICON TRANSISTOR

JEDEC TO-18 CASE

DESCRIPTION:

The CENTRAL SEMICONDUCTOR 2N2411, 2N2412 types are PNP Saturated Switching Transistors designed for high speed switching applications.

MAXIMUM RATINGS:

	SYMBOL		UNITS
Collector-Base Voltage	V_{CBO}	25	V
Collector-Emitter Voltage	V_{CEO}	15	V
Emitter-Base Voltage	V_{EBO}	5.0	V
Collector Current	I_C	100	mA
Power Dissipation	P_D	0.5	W
Power Dissipation ($T_C=25^\circ\text{C}$)	P_D	1.2	W
Operating and Storage Junction Temperature	T_J, T_{stg}	-65 to +200	$^\circ\text{C}$
Thermal Resistance	θ_{JA}	350	$^\circ\text{C/W}$
Thermal Resistance	θ_{JC}	146	$^\circ\text{C/W}$

ELECTRICAL CHARACTERISTICS:


SYMBOL	TEST CONDITIONS	2N2411		2N2412		UNITS
		MIN	MAX	MIN	MAX	
I_{CES}	$V_{CE}=15\text{V}$		10		10	nA
I_{CES}	$V_{CE}=15\text{V}, T_A=150^\circ\text{C}$		10		10	μA
I_{EBO}	$V_{EB}=5.0\text{V}$				10	μA
BV_{CBO}	$I_C=10\mu\text{A}$	25		25		V
BV_{CEO}	$I_C=10\text{mA}$	15		15		V
$V_{CE(SAT)}$	$I_C=10\text{mA}, I_B=1.0\text{mA}$		0.2		0.2	V
$V_{BE(SAT)}$	$I_C=10\text{mA}, I_B=1.0\text{mA}$	0.7	0.9	0.7	0.9	V
h_{FE}	$V_{CE}=0.5\text{V}, I_C=50\mu\text{A}$	10		20		
h_{FE}	$V_{CE}=0.5\text{V}, I_C=10\text{mA}$	20	60	40	120	
h_{FE}	$V_{CE}=0.5\text{V}, I_C=10\text{mA}, T_A=-55^\circ\text{C}$		10		20	
h_{FE}	$V_{CE}=1.0\text{V}, I_C=50\text{mA}$	10		20		
h_{fe}	$V_{CE}=10\text{V}, I_C=10\text{mA}, f=100\text{MHz}$	1.4		1.4		
C_{ob}	$V_{CB}=5.0\text{V}, I_E=0, f=1.0\text{MHz}$		5.0		5.0	pF
C_{ib}	$V_{EB}=0.5\text{V}, I_C=0, f=1.0\text{MHz}$		8.0		8.0	pF

(CONTINUED ON REVERSE SIDE)

ELECTRICAL CHARACTERISTICS (Continued)

SYMBOL	TEST CONDITIONS	2N2411		2N2412		UNITS
		MIN	MAX	MIN	MAX	
t_d	$V_{BE(off)}=1.2V$, $I_C=10mA$, $I_{B1}=2.5mA$, $R_L=300\Omega$		10		10	ns
t_r	$V_{BE(off)}=1.2V$, $I_C=10mA$, $I_{B1}=2.5mA$, $R_L=300\Omega$		20		20	ns
t_{on}	$V_{BE(off)}=1.2V$, $I_C=10mA$, $I_{B1}=2.5mA$, $R_L=300\Omega$		25		25	ns
t_s	$I_C=10mA$, $I_{B1}=2.5mA$, $I_{B2}=2.0mA$, $R_L=300\Omega$		90		90	ns
t_f	$I_C=10mA$, $I_{B1}=2.5mA$, $I_{B2}=2.0mA$, $R_L=300\Omega$		20		20	ns
t_{off}	$I_C=10mA$, $I_{B1}=2.5mA$, $I_{B2}=2.0mA$, $R_L=300\Omega$		100		100	ns

JEDEC TO-18 CASE - MECHANICAL OUTLINE



DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A (DIA)	0.209	0.230	5.31	5.84
B (DIA)	0.178	0.195	4.52	4.95
C	-	0.030	-	0.76
D	0.170	0.210	4.32	5.33
E	0.500	-	12.70	-
F (DIA)	0.016	0.019	0.41	0.48
G (DIA)	0.100		2.54	
H	0.050		1.27	
I	0.036	0.046	0.91	1.17
J	0.028	0.048	0.71	1.22

TO-18 (REV: R1)

Lead Code:

- 1) Emitter
- 2) Base
- 3) Collector

CentralTM
Semiconductor Corp.

145 Adams Ave., Hauppauge, NY 11788 USA
Phone (631) 435-1110 FAX (631) 435-1824

Manufacturers of World Class Discrete Semiconductors
www.centralsemi.com