


Product Area Male cable connector, metal locking system, screw termination
M12 connectors A-Coding serie 713

Pole 8
Article number 99 0487 12 08


illustration



scale drawing



Contact Arrangement



	X	Y
1	2,69	0,57
2	0,57	2,69
3	-1,66	2,20
4	-2,75	0,19
5	-1,94	-1,94
6	0,19	-2,74
7	2,20	-1,65
8	0,00	0,00

You can find the item description and assembly instruction on the next page.

Technical data

Common values

Connector Design	Male cable connector
Connector locking system	Screw-locking
Termination	screw
Wire gauge (mm)	0,50 mm ²
Wire gauge (AWG)	20
Upper temperature	+85 °C
Lower temperature	-40 °C

Material

Material of contact	CuZn (brass)
Contact plating	Au (gold)
Material of contact body	PA
Material of housing	PA

Cable data

Electrical values

Rated voltage	60 V
Rated impulse voltage	800 V
Pollution degree	3
Overvoltage category	II
Material group	III
Rated current (40 °C)	2 A
Volume resistivity	≤ 3 mΩ
Degree of protection	IP 67
Mechanical operation	>100 mating cycles

Contacts 8: cable outlet: 6-8 mm, Male cable connector, metal locking system, screw termination




Product Male cable connector, metal locking system, screw termination
Area M12 connectors A-Coding serie 713

Pole 8
Article number 99 0487 12 08

Date: 2013-06-04 - Page 2 of 2

Item description



Installation instructions / Mounting cutout

