



-
- A diagram of a 10-pin D-sub connector. The connector has a D-shaped top with five pins on the left and five on the right. The pins are numbered 1 through 10 in a grid. The top row contains pins 1, 2, 3, 4, and 5. The bottom row contains pins 6, 7, 8, 9, and 10. The pins are arranged in a 2x5 grid.
- | | | | | |
|---|---|---|---|----|
| 1 | 2 | 3 | 4 | 5 |
| 6 | 7 | 8 | 9 | 10 |

- △6. INDICATED PREFIX AND ID MARK OF PRODUCT P/N BY COLOR HOT MARK

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 12FEB08		 TE Connectivity					
		CHK K.BETSUI 12FEB08							
DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称					
		APVD K.BETSUI 12FEB08 PRODUCT SPEC 製品規格 SEE NOTE 4		26POSITION CAP HOUSING ASSEMBLY 040/070 SERIES HYBRID I/O CONNECTOR					
		APPLICATION SPEC 取付適用規格 —							
MATERIAL 材料		FINISH 仕上		SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO		
HOUSING : PBT CONTACT : BRASS		WEIGHT 12.6 g		A2	00779	C=178762	—		
CUSTOMER DRAWING						SCALE 尺度	2:1	SHEET 1 of 1	REV F6