





Dimensions mm[inch]

tolerances acc. to DIN ISO 2768-m
Toleranzen gem. DIN ISO 2768-m



Isometric

Scale 1:2
Maßstab 1:2




Cable

PVC LIYY 2x0,25qmm
colour of mantle: grey
colour of wires: white, brown
PVC LIYY 2x0,25qmm
Mantelfarbe: grau
Aderfarben: weiß, braun

Terminals/Connector


Ends tinned
Enden verzinkt

Schematic




Marking

according to EN60062/factory code
gem. EN60062/Fertigungsstätte



Housing





Products for tomorrow...

Europe: +49 / 7731 8399 0

| Email: info@meder.com

USA: +1 / 508 295 0771

| Email: salesusa@meder.com

Asia: +852 / 2955 1682

| Email: salesasia@meder.com

Item No.:

2224715054

Item:

MK02/4-1A66E-500W

MK02/4-1A71E-500W

Magnetic properties	Conditions	Min	Typ	Max	Unit
Pull in	at 20°C	77		115	AT
Test equipment		KMS-11			

Special Product Data	Conditions	Min	Typ	Max	Unit
Contact - No.		66			
Contact - form		A - NO			
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
operating voltage	DC or Peak AC			180	V
operating ampere	DC or Peak AC			1,25	A
Switching current	DC or Peak AC			0,5	A
Sensor-resistance	measured with 40% overdrive Sensor deactivated			220	mOhm
Housing material		PBT glass fibre reinforced			
Case color		blue			
Sealing compound		Polyurethan			

Environmental data	Conditions	Min	Typ	Max	Unit
Operating temperature	cable not moved	-30		80	°C
Operating temperature	cable moved	-5		80	°C
Storage temperature		-30		80	°C

Cable specification	Conditions	Min	Typ	Max	Unit
Cable typ		round cable			
Cable material		PVC			
Cross section		0,25 qmm			

General data	Conditions	Min	Typ	Max	Unit
Mounting advice		from 5m cable, a pre-resistor is recommended.			
Mounting advice		Decreased switching distances by mounting on iron.			
Mounting advice		Don't use magnetically conductive screws			
tightening torque	Screw M3 ISO 1207 Disk ISO 7089			0,5	Nm

Modifications in the sense of technical progress are reserved

Designed at: 10.10.06 Designed by: KSCHIELENSKI

Approval at: 05.11.07 Approval by: BUELTZHOEFFER

Last Change at: 16.11.12 Last Change by: OMUELLER

Approval at: 16.11.12 Approval by: TFRITSCHI

Version: 04