

**MOC205 , MOC206 , MOC207 , MOC208,
MOC211 , MOC212 , MOC213 ,
MOC215 , MOC216 , MOC217**



SMALL OUTLINE OPTICALLY COUPLED ISOLATOR TRANSISTOR OUTPUT

DESCRIPTION

This series of optically coupled isolators consist of a Gallium Arsenide infrared emitting diode and NPN silicon photo transistor mounted in a standard 8 pin SOIC package, which makes them ideally suited for high density applications with limited space.

FEATURES


- Standard SOIC-8 Footprint with 0.05" Lead Spacing
- Specified min. and max. CTR at $10\text{mA } I_F$, $10\text{V } V_{CE}$
MOC205, 40 - 80%
MOC206, 63 - 125%
MOC207, 100 - 200%
MOC208, 160 - 320%
- Specified minimum CTR at $10\text{mA } I_F$, $10\text{V } V_{CE}$
MOC211, 20%
MOC212, 50%
MOC213, 100%
- Specified minimum CTR at $1\text{mA } I_F$, $5\text{V } V_{CE}$
MOC215, 20%
MOC216, 50%
MOC217, 100%
- Isolation Voltage, $2500\text{V}_{\text{RMS}}$
- High BV_{CEO} (70V min)
- All electrical parameters 100% tested
- Available in Tape and Reel - add suffix " T & R "
- Custom electrical selections available

ABSOLUTE MAXIMUM RATINGS (25°C unless otherwise noted)

Storage Temperature _____ -55°C to +125°C
Operating Temperature _____ -55°C to +100°C
Lead Soldering Temperature _____ 260°C
(single wave for 10 secs)
Input to Output Isolation Voltage _____ 2500V_{RMS}

INPUT DIODE

Forward Current _____ 60mA
Reverse Voltage _____ 6V
Peak Forward Current (tp ≤ 10μs) _____ 3A
Power Dissipation _____ 100mW
(derate linearly 1.33mW/°C above 25°C)
Junction Temperature _____ 125°C



APPLICATIONS

- Computer terminals
- Industrial systems controllers
- Hybrid substrates that require high density mounting
- Signal transmission between systems of different potentials and impedances

OUTPUT TRANSISTOR

Collector-emitter Voltage BV_{CEO} _____ 70V
Emitter-collector Voltage BV_{ECO} _____ 7V
Collector-base Voltage BV_{CBO} _____ 70V
Collector Current _____ 50mA
Collector Current _____ 100mA
(pw ≤ 10ms , 50% duty ratio)
Power Dissipation _____ 150mW
(derate linearly 2.00mW/°C above 25°C)
Junction Temperature _____ 125°C

PACKAGE

Total Power Dissipation _____ 250mW
(derate linearly 3.3mW/°C above 25°C)

ISOCOM COMPONENTS LTD

Unit 25B, Park View Road West,
Park View Industrial Estate, Brenda Road
Hartlepool, Cleveland, TS25 1YD
Tel: (01429) 863609 Fax: (01429) 863581

ISOCOM INC

1024 S. Greenville Ave, Suite 240,
Allen, TX 75002 USA
Tel: (214) 495-0755 Fax: (214) 495-0901
e-mail info@isocom.com
http://www.isocom.com

ELECTRICAL CHARACTERISTICS (25°C unless otherwise noted)

	PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Input	Forward Voltage (V_F) Capacitance Reverse Current (I_R)		1.2 50	1.5 100	Volt pF μA	$I_F = 10 \text{ mA}$ $V_R = 0, f = 1 \text{ MHz}$ $V_R = 6 \text{ V}$
Output	Collector-emitter Voltage (BV_{CEO}) Emitter-collector Voltage (BV_{ECO}) Collector-base Voltage (BV_{CBO}) Collector-emitter Dark Current (I_{CEO})	70 7 70		50	Volt Volt Volt nA	$I_C = 100 \mu A$ $I_E = 100 \mu A$ $I_C = 100 \mu A$ $V_{CE} = 10 \text{ V}$
Coupled	Current Transfer Ratio (CTR) MOC205 MOC206 MOC207 MOC208 MOC211 MOC212 MOC213 MOC205 MOC206 MOC207 MOC208 MOC215 MOC216 MOC217 Collector-emitter Saturation Voltage $V_{CE(SAT)}$ (MOC205 to MOC213) Collector-emitter Saturation Voltage $V_{CE(SAT)}$ (MOC215 to MOC217) Capacitance Input to Output (C_{ISO}) Input to Output Isolation Resistance (R_{ISO}) Input to Output Isolation Voltage (V_{ISO}) Output Turn on Time (t_{on}) Output Turn off Time (t_{off}) Output Rise Time (t_r) Output Fall Time (t_f)	40 63 100 160 20 50 100 13 22 34 56 20 50 100 2500	 0.3 10 ¹¹ 3.0 3.0 1.6 2.2	80 125 200 320 0.4 0.4	% % % % % % % % % % % % % % pF Ω V_{RMS} μs μs μs μs	$I_F = 10 \text{ mA}, V_{CE} = 10 \text{ V}$ $I_F = 1 \text{ mA}, V_{CE} = 10 \text{ V}$ $I_F = 1 \text{ mA}, V_{CE} = 5 \text{ V}$ $I_F = 10 \text{ mA}, I_C = 2 \text{ mA}$ $I_F = 1 \text{ mA}, I_C = 0.1 \text{ mA}$ $f = 1 \text{ MHz}$ (note 1) $V_{IO} = 500 \text{ V}$ (note 1) Note 1 $I_C = 2 \text{ mA},$ $V_{CC} = 10 \text{ V}, R_L = 100 \Omega$

Note 1. Measured with input leads shorted together and output leads shorted together.






FIG 1


Collector Power Dissipation vs. Ambient Temperature




Current Transfer Ratio vs. Forward Current




Forward Current vs. Ambient Temperature



Current Transfer Ratio vs. Forward Current



Relative Current Transfer Ratio vs. Ambient Temperature



Current Transfer Ratio vs. Forward Current

