




SMA

Panel Jack Receptacles – 2-hole Flange

Amphenol®




Fig. 1



.223" Wide 2-Hole Trimline Flange

SMA Panel Jack Receptacles
Slot Terminal
901-9244-1 ‡
Gold Plated
901-9244-1SF ‡
Passivated Finish

Fig. 2



.223" Wide 2-Hole Trimline Flange

SMA Panel Jack Receptacles
Socket Terminal
901-9814
Flush TFE,
Conductive Epoxy Cap
901-9770
.185 Exposed TFE

SMA PANEL RECEPTACLES – 2-hole trimline flange

Description	Terminal Type	Plt.	Ins.	Construction Notes		Amphenol Number	Fig.
Panel Jack Receptacle	Slot .025" (0.6mm) wide	P9	D1	Contact Shipped Unassembled/ .025" (0.6 mm) Exposed TFE	Gold Plated	‡ 901-9244-1	1
		P13	D1		Passivated	‡ 901-9244-1SF	1
Panel Jack Receptacle	Socket	P13	D1	Flush TFE	Passivated Body	901-9814	2
Panel Jack Receptacle	Socket	P13	D1	.085 Exposed TFE	Passivated Body	901-9770	2

‡ Contact shipped unassembled. User has option for slot orientation

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[901-9244-1SF](#) [901-9770](#)