




Features:

- For surface mounted application.
- Easy pick and place.
- Metal to silicon rectifier, majority carrier conduction.
- Low power loss, high efficiency.
- High current capability, low V_F .
- High surge current capability.
- Plastic material.
- Epitaxial construction.
- High temperature soldering: 260°C/10 seconds at terminals.

SMA/DO-214AC



Dimensions : Inches (Millimetres)

Mechanical Data:

Cases	: JEDEC SMA/DO-214AC moulded plastic.
Terminals	: Pure tin plated, lead free.
Polarity	: Indicated by cathode band.
Packing	: 12mm tape per EIA STD RS-481.
Weight	: 0.066 gram.

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Type Number	Symbol	SS12	SS13	SS15	SS19	SS115	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	20	30	50	90	150	V
Maximum RMS Voltage	V _{RMS}	14	21	35	63	105	
Maximum DC Blocking Voltage	V _{DC}	20	30	50	90	150	
Maximum Average Forward Rectified Current at T _L	I _(AV)	1.0					A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	30					
Maximum Instantaneous Forward Voltage (Note 1) I _F = 1.0A at 25°C at 100°C	V _F	0.5 0.4		0.75 0.65	0.80 0.70	0.95 0.85	V
Maximum DC Reverse Current at T _A = 25°C at Rated DC Blocking Voltage at T _A = 125°C	I _R	0.4			0.1		μA μA
		10		5.0	2.0		
Maximum DC Reverse Current at V _R = 33V and T _A = 50°C	HT _{IR}	-			5.0		μA
Typical Junction Capacitance (Note 3)	C _j	50					pF
Typical Thermal Resistance (Note 2)	R _{θJL}	28					°C/W
	R _{θJA}	88					
Operating Temperature Range	T _J	-65 to +125		-65 to +150			°C
Storage Temperature Range	T _{STG}	-65 to +150					


Notes: 1. Pulse Test with PW = 300 μ seconds, 1% Duty Cycle.

2. Measured on PC Board with 0.2 x 0.2 inches (5.0mm x 5.0mm) Copper Pad Areas.


3. Measured at 1MHz and Applied Reverse Voltage of 4.0V dc.

Ratings and Characteristic Curves (SS115, SS12, SS13, SS15, SS19)


Maximum Forward Current Derating Curve




Maximum Non-Repetitive Forward Surge Current




Typical Forward Characteristics




Typical Reverse Characteristics



Typical Junction Capacitance



Typical Transient Thermal Characteristics



Part Number Table

Description	Part Number
Diode, Schottky, 1A, 150V	SS115
Diode, Schottky, 1A, 20V	SS12
Diode, Schottky, 1A, 300V	SS13
Diode, Schottky, 1A, 50V	SS15
Diode, Schottky, 1A, 90V	SS19

Notes:

International Sales Offices:

	AUSTRALIA – Farnell Tel No: ++61 1300 361 005 Fax No: ++61 1300 361 225		FINLAND – Farnell Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411		ITALY – Farnell Tel No: ++ 39 02 93 995 200 Fax No: ++ 39 02 93 995 300		SPAIN – Farnell Tel No: 901 20 20 80 Fax No: 901 20 20 90
	AUSTRIA – Farnell Tel No: ++ 43 662 2180 680 Fax No: ++ 43 662 2180 670		FRANCE – Farnell Tel No: ++ 33 474 68 99 99 Fax No: ++ 33 474 68 99 90		MALAYSIA – Farnell-Newark Tel No: ++ 60 3 7873 8000 Fax No: ++ 60 3 7873 7000		SWEDEN – Farnell Tel No: ++ 46 8 730 50 00 Fax No: ++ 46 8 83 52 62
	BELGIUM – Farnell Tel No: ++ 32 3 475 2810 Fax No: ++ 32 3 227 3648		GERMANY – Farnell Tel No: ++ 49 89 61 39 39 39 Fax No: ++ 49 89 613 59 01		NETHERLANDS – Farnell Tel No: ++ 31 30 241 7373 Fax No: ++ 31 30 241 7333		SWITZERLAND – Farnell Tel No: ++ 44 204 64 64 Fax No: ++ 44 204 64 54
	BRAZIL – Farnell-Newark Tel No: ++ 55 11 4066 9400 Fax No: ++ 55 11 4066 9410		HONG KONG – Farnell-Newark Tel No: ++ 852 2268 9888 Fax No: ++ 852 2268 9899		NEW ZEALAND – Farnell Tel No: 0800 90 80 80 Fax No: 0800 90 80 81		UK – Farnell Tel No: ++ 44 8701 200 200 Fax No: ++ 44 8701 200 201
	CHINA – Farnell-Newark Tel No: ++86 10 6238 5152 Fax No: ++86 10 6238 5022		HUNGARY – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		NORWAY – Farnell Tel No: 800 146 70 Fax No: 800 146 76		UK – CPC ++ 44 8701 202 530 ++ 44 8701 202 531
	CZECH REPUBLIC – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		INDIA – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209		PORTUGAL – Farnell Tel No: ++ 34 93 475 8804 Fax No: ++ 34 93 474 5288		USA – Newark Tel No: 800 463 9275
	DENMARK – Farnell Tel No: ++ 45 44 53 66 44 Fax No: ++ 45 44 53 66 06		IRELAND – Farnell Tel No: ++ 353 1 830 9277 Fax No: ++ 353 1 830 9016		RUSSIA – Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209	 EXPORT – Farnell Tel No: ++ 44 8701 200 208 Fax No: ++ 44 8701 200 209 For enquiries from all other markets	
	ESTONIA – Farnell Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411		ISRAEL – Farnell Tel No: ++ 180 937 0015 Fax No: ++ 180 937 0014		SINGAPORE – Farnell-Newark Tel No: ++ 65 6788 0200 Fax No: ++ 65 6788 0300		

<http://www.farnell.com>
<http://www.newark.com>
<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.