

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY

PROPORT, ILLINOIS

FED. MFR. CODE 91929

SWITCH-BASIC

CATALOG LISTING

ISE 2-T

ISE 2-T

M

DRAWING NUMBER

ISSUE X2

3

REPLACES

RELEASE NO. SR 10107

CHECK

REVISIONS

A	CO-34213
J A L	24 SEPT 74
B	CO-57041-A
C J H	26 MAR 85

28 FEB 62

CHECK DRY


28 FEB 62

CHECK DAW

27 FEB 62

M B F

FO-50378



NOTE -

- △ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
- △ ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — — — 5-17 OZ	CONTACT ARRANGEMENT S P N C	DO NOT SCALE PRINT
RELEASE FORCE — — — — — 4 OZ MIN	250 VAC — — — — — 5 AMP	UNLESS OTHERWISE SPECIFIED
RELEASE TRAVEL — — — — — .004 MIN	30 VOLTS DC RATING	DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL — — — — — .004 MAX	INDUCTIVE — — — — — SEA LEVEL — — — 3 AMP	TOLERANCES ARE:
OVERTRAVEL — — — — — .003 MIN	RESISTIVE — — — — — 50,000 FT — — — 2.5 AMP	ONE PLACE (.0) ± .030
	MAXIMUM INRUSH — — — — — 50,000 FT — — — 5 AMP	TWO PLACE (.00) ± .015
		THREE PLACE (.000) ± .005
		ANGLES ±
		WEIGHT .26 OZ MAX