


10/100BASE-TX Single-Port Transformer Modules

Military / Aerospace Grade



- Compliant with IEEE 802.3u & ANSI X3.263 standards
- 350 μ H OCL with 8mA bias, MSL: 3
- Operating and storage temperature:
100B-1001F & 100B-1003: -40°C to +85°C
100B-1001FX & 100B-1003X: -55°C to +125°C
- IC grade transfer-molded package withstands
235°C peak temperature profile. RoHS version withstands 245°C
- AS9100C Certified (Based on and including ISO 9001:2008)

Electrical Specifications @ 25°C

Part Number ¹	Insertion Loss (dB MIN)	Return Loss (dB MAX)				Crosstalk (dB MAX)				DMtoCM Rejection Ratio (dB MAX)		
	0.1-100 MHz	2-30 MHz	50 MHz	60 MHz	80 MHz	16 MHz	30 MHz	60 MHz	80 MHz	0.1-30 MHz	30-60 MHz	60-100 MHz
100B-1001F	-1.00	-18	-14	-12	-12	-48	-44	-40	-38	TX: -50 RX: -50	TX: -40 RX: -40	TX: -30 RX: -30
100B-1001FX	-1.10	-18	-14	-12	-10	-48	-44	-40	-38	TX: -45 RX: -45	TX: -40 RX: -40	TX: -38 RX: -33
100B-1003	-1.00	-20	-14	-12	-12	-48	-45	-40	-38	TX: -50 RX: -50	TX: -40 RX: -40	TX: -35 RX: -35
100B-1003F	-1.00	-20	-14	-12	-12	-48	-45	-40	-38	TX: -50 RX: -50	TX: -40 RX: -40	TX: -35 RX: -35
100B-1003X	-1.00	-20	-14	-12	-12	-48	-45	-40	-38	TX: -45 RX: -35	TX: -40 RX: -35	TX: -35 RX: -35

NOTES: 1. Add suffix NL for RoHS compliant version; i.e. 100B-1001F becomes 100B-1001FNL. NL Parts are 100% Sn.
2. For Tape & Reel Packaging, add "T" suffix at the end of the part number; i.e. 100B-1003XT



3. Lead Finish: Sn63/Pb37
4. 100B-1003FNL has a Lead
5. 100B-1003FNL - MSL: 4

6. Maximum Hi-Pot 1800VAC/2500VDC for 6 Sec.

Mechanical

Schematic

100B-1001F/X



10/100BASE-TX Single-Port Transformer Modules



Military / Aerospace Grade



Mechanical

Schematic

100B-1003/X/FNL



Weight 1.16 grams
 Tape and Reel 600/reel

Dimensions: Inches
 mm
 Unless otherwise specified, all tolerances are $\pm .010$
 0,25

For More Information

Pulse North America Headquarters
 Two Pearl Buck Court
 Bristol, PA 19007
 U.S.A.

Tel: 215 781 6400
 Fax: 215 781 6403

Pulse Europe
 Einsteinstrasse 1
 D-71083 Herrenberg
 Germany

Tel: 49 7032 7806 0
 Fax: 49 7032 7806 135

Pulse China Headquarters
 B402 Shenzhen Academy of
 Aerospace Technology Bldg.
 10th Kejinan Road
 High-Tech Zone
 Nanshan District
 Shenzhen, P.R. China 518057
 Tel: 86 755 33966678
 Fax: 86 755 33966700

Pulse North China
 Room 2704/2705
 Super Ocean Finance Ctr.
 2067 Yan An Road West
 Shanghai 200336
 China

Tel: 86 21 62787060
 Fax: 86 21 62786973

Pulse South Asia
 135 Joo Seng Road
 #03-02
 PM Industrial Bldg.
 Singapore 368363

Tel: 65 6287 8998
 Fax: 65 6287 8998

Pulse North Asia
 3F, No. 198
 Zhongyuan Road
 Zhongli City
 Taoyuan County 320
 Taiwan R. O. C.
 Tel: 886 3 4356768
 Fax: 886 3 4356823 (Pulse)
 Fax: 886 3 4356820 (FRE)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2014, Pulse Electronics, Inc. All rights reserved.