





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G	REVISED PER ECO-14-000260	07JUL2014	NK	MM



RECOMMENDED HOLE LAYOUT

- | | |
|---|---|
| 1 | TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD |
| 2 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING |
| 3 | RETENTION FEATURE ON SOLDEDTAILS LOCATED AT MANUFACTURER'S OPTION. |
| 4 | THIS DIMENSION WILL BE 4.67±0.41 [1.84±.016] FOR THE 2 POSITION CONFIGURATION |
| 5 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

OBSOLETE 5	101.19	[3.984]	99.06	[3.900]	39	80	4-146426-0
	98.65	[3.884]	96.52	[3.800]	38	78	3-146426-9
	96.11	[3.784]	93.98	[3.700]	37	76	3-146426-8
	93.57	[3.684]	91.44	[3.600]	36	74	3-146426-7
	91.03	[3.584]	88.90	[3.500]	35	72	3-146426-6
	88.49	[3.484]	86.36	[3.400]	34	70	3-146426-5
	85.95	[3.384]	83.82	[3.300]	33	68	3-146426-4
	83.41	[3.284]	81.28	[3.200]	32	66	3-146426-3
	80.87	[3.184]	78.74	[3.100]	31	64	3-146426-2
	78.33	[3.084]	76.20	[3.000]	30	62	3-146426-1
	75.79	[2.984]	73.66	[2.900]	29	60	3-146426-0
	73.25	[2.884]	71.12	[2.800]	28	58	2-146426-9
	70.71	[2.784]	68.58	[2.700]	27	56	2-146426-8
	68.17	[2.684]	66.04	[2.600]	26	54	2-146426-7
	65.63	[2.584]	63.50	[2.500]	25	52	2-146426-6
	63.09	[2.484]	60.96	[2.400]	24	50	2-146426-5
	60.55	[2.384]	58.42	[2.300]	23	48	2-146426-4
	58.01	[2.284]	55.88	[2.200]	22	46	2-146426-3
	55.47	[2.184]	53.34	[2.100]	21	44	2-146426-2
	52.93	[2.084]	50.80	[2.000]	20	42	2-146426-1
	50.39	[1.984]	48.26	[1.900]	19	40	2-146426-0
	47.85	[1.884]	45.72	[1.800]	18	38	1-146426-9
	45.31	[1.784]	43.18	[1.700]	17	36	1-146426-8
	42.77	[1.684]	40.64	[1.600]	16	34	1-146426-7
	40.23	[1.584]	38.10	[1.500]	15	32	1-146426-6
	37.69	[1.484]	35.56	[1.400]	14	30	1-146426-5
	35.15	[1.384]	33.02	[1.300]	13	28	1-146426-4
	32.61	[1.284]	30.48	[1.200]	12	26	1-146426-3
	30.07	[1.184]	27.94	[1.100]	11	24	1-146426-2
	27.53	[1.084]	25.40	[1.000]	10	22	1-146426-1
	24.99	[.984]	22.86	[.900]	9	20	1-146426-0
	22.45	[.884]	20.32	[.800]	8	18	146426-9
	19.91	[.784]	17.78	[.700]	7	16	146426-8
17.37	[.684]	15.24	[.600]	6	14	146426-7	
14.83	[.584]	12.70	[.500]	5	12	146426-6	
12.29	[.484]	10.16	[.400]	4	10	146426-5	
9.75	[.384]	8.99	[.300]	3	8	146426-4	
7.21	[.284]	6.45	[.200]	2	6	146426-3	
4.67	[.184]	2.54	[.100]	1	4	146426-2	
2.33	[.092]	-	-	-	2	146426-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 65295 T. HOFFMAN GWK G. DUBNICZKI 20C195		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PL/C ± — 1 PL/C ± — 2 PL/C ± 0.13[.005] 3 PL/C ± — 4 PL/C ± — ANGLES ± —		NAME HEADER ASSY, MOD II, BREAKAWAY, DBL ROW, .100 X 100 CL, VERT, .025 SQ POSTS, WITH RETENTION FEATURE	
		APPLIC. SPEC —		SIZE CAGE CODE DRAWING NO A1 00779 C=146426	
MATERIAL FINISH HOUSING: FLAME RETARDANT POLYIMIDE COLLAR: BLACK POST: COPPER ALLOY		WEIGHT — CUSTOMER DRAWING		RESTRICTED TO —	
POSTS: 0.0051[.00050] DSGS: DUPLEX		SCALE 4:1		SHEET 1 OF 1 REV G	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-146426-0](#)