

Electronic Level: Manufacturers Code 59-017-150



Large 11mm LCD Display with optional backlight illumination
 Steel Working Surfaces
 Display Option: Degrees for Angles or % for Inclination
 Measuring Range Angles: 360 degrees in 4 x 90 degree segments
 Measuring Range Inclination: 0 – 100% in 8 x 45 degree segments (100% = 45 degrees)
 Resolution: Angles 0.1degree, Inclination 0.1%
 Accuracy: Angles 0.3 degree, Inclination 0.2%
 Display inverts automatically for use on underside of work piece
 Audible Signal: 0, 10, 20, 30, 40, 50, 60, 70, 80, & 90°
 Dimensions: 150 x 50 x 33mm
 Power: 3 x CR 2032 lithium cells



Button Functions

- 1 Power: ON/OFF
- 2 Backlight/Audible Angle Alarm (beep)
- 3 Degree/Slope percentage selection
- 4 Absolute/Relative display selection
- 5 Hold

Audible Beep can be selected to indicate Zero and each 10 degree position up to 90 degrees

Measurement Data Hold: Press Hold Button once to hold display value (Direction Arrows will flash)

Press Hold Button to release Display Hold

Calibrate Button sets zero at any desired start position.

Original Zero is resumed following Power Down and new Start.

Auto Power Shut Off: 4 minutes, plus low battery warning

Power Supply: 3 x CR 2032 3V Lithium Batteries

Operating Temperature: 0 – 40 degrees Centigrade

Dimensions: 155 x 53 x 28mm

Weight: 310 grms.