



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS				
ltr	ecn no	dr	date		tolerances unless otherwise specified						title			
L	V82054	EPK	11/12/98		angles	linear		.XX±.01/.3		VRM 8 HEADER ASS'Y				
M	V82161	EPK	12/10/98					.XXX±.005/.13						
N	V91079	EPK	5/10/99		0'±2'		.XXX±.0020/.051							
P	V01868	MDF	7/31/00		dr	M. CLOUSER		6/12/95				dwg no		
R	V03-1222	PJ	11/18/03		engr	L. FYE		6/12/95				sheet 1 of 4		size
S	V04-0262	HTB	3/18/04		chr	L. FYE		6/12/95				95798		A.
T	M06-0289	AGS	7/29/06		appd	L. FYE		6/12/95				type		Product Customer Drawing
sheet index		revision sheet		T	T	T	T							
				1	2	3	4							




- ① MOLDED MATERIAL: HIGH TEMP RESIN
PER UL 94 V-0
COLOR: PANTONE 4545 (OFF WHITE).
- ② PIN MATERIAL: 3/4 HARD PHOS BRONZE
UNS C51000.
- ③ PIN RETENTION TO BE 3 LB/1.36 KG
MIN IN EITHER DIRECTION.
- ④ SURFACE INDICATED MUST BE PARALLEL TO
DATUM -C- WITHIN $\pm 4^\circ$.
- ⑤ "R" FOLLOWING P/N INDICATES RETENTION
FEATURE.
- ⑥ PRESS FIT PINS 95798-5XX SERIES.
- ⑦ OPTIONAL POLARIZING FEATURE.
- ⑧ CRITICAL CONTACT AREA ON ALL FOUR SIDES.
- ⑨ PACKAGE IN PLASTIC TRAYS.
- ⑩ LUBRICATION - (ZIP-CHEM TO C-26)


[illegible]

PRODUCT NUMBER


SEE TABLE



DETAIL "G"
ROTATED 90°
SCALE 3:1
NOTE 5



DETAIL "H"
PRESS-FIT TAILS
ROTATED 90°
SCALE 3:1
NOTE 6



DETAIL "M"
SCALE 3:1
NOTE 7

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection FIRST ANGLE	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
T					angles	.XX±.01/.3	VRM 8 HEADER ASS'Y
					linear	.XXX±.005/.13	
					0°±2'	.XXXX±.0020/.051	
			dr	M. CLOUSER	6/12/95	scale 1:1	
			enr	L. FYE	6/12/95		
			chr	L. FYE	6/12/95		
			appd	L. FYE	6/12/95		
sheet index	revision sheet						dwg no 95798 type Product Customer Drawing

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER	CONTACT PLATING	TAIL LENGTH	TAIL PLATING	POLARIZING PEG	LUBRICATION NOTE 11
95798-001			U N A V A I L A B L E		
-002	15u"/0.38 GXT OVER 50u"/1.27u Ni	.122/3.10	15μ"/0.38μ GXT OVER 50μ"/1.27μ Ni	NO	NO
-003			U N A V A I L A B L E		
-011			U N A V A I L A B L E		
-012			U N A V A I L A B L E		
-201			U N A V A I L A B L E		
-202			U N A V A I L A B L E		
-203			U N A V A I L A B L E		
-204			U N A V A I L A B L E		
-301			U N A V A I L A B L E		
95798-502			U N A V A I L A B L E		

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS			
ltr	ecn	no	dr	date		tolerances unless otherwise specified							
T						angles	.XX±.01/.3		INCH/MM		title VRM 8 HEADER ASS'Y		
						linear	.XXX±.005/.13						
						0°±2'	.XXXX±.0020/.051		scale 1:1				
						dr	M. CLOUSER	6/12/95			dwg no 95798		
						enr	L. FYE	6/12/95				sheet4 of 4	size
						chr	L. FYE	6/12/95				A3	
						appd	L. FYE	6/12/95					
sheet index		revision sheet								type Product Customer Drawing			