



Features

- DC to 4 GHz
- Flanged model
- Low VSWR

Applications

- High power RF transmission

CHF5225CNF Series 60 W Power RF Flanged Chip Termination


General Specifications

Substrate.....ALN
Resistive Film.....Thick Film
TabAg
Protection.....Epoxy
Tab Attachment
.....Braze with Epoxy Encapsulation
Mounting FlangeCu plated with Ni
Resistance.....50 Ω
Tolerance..... $\pm 5\%$
Packaging100 pcs./box

Absolute Ratings


Power.....60 W
Frequency4.0 GHz
VSWR.....1.2 Maximum

Characteristic Curve




Product Dimensions

Version C



Version D



DIMENSIONS = $\frac{\text{MILLIMETERS}}{(\text{INCHES})}$

How To Order

CHF 5225 C N F 500 L

Model _____
Size _____
Version _____
Substrate _____
Mount _____
F = Flange
Value _____
500 = 50 Ohm
Function _____
L = Termination



Reliable Electronic Solutions

Asia-Pacific:

Tel: +886-2 2562-4117
Fax: +886-2 2562-4116

Europe:

Tel: +41-41 768 5555
Fax: +41-41 768 5510

The Americas:

Tel: +1-951 781-5500
Fax: +1-951 781-5700

www.bourns.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[CHF5225CNF500L](#) [CHF5225DNF500L](#)