

CATALOG LISTING

1EN42-R8

PAGE 1 OF 1

REPLACES

PR-22476

CHECK

REVISIONS

A

PR-22476

MAM

27 NOV 96

CHECK

CHECK





DDM/CAD

DRAWN

M A M

27NOV96

CHECK



- NOTES
- 1 — CORROSION RESISTANT STEEL ENCLOSURE
 - 2 — SWITCH SEALED PER MIL-S-8805 SYMBOL 4
 - 3 — COINCIDENCE OF OPERATING AND RELEASING POINTS: $.010$ OF PLUNGER TRAVEL
 - 4 — CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - (5) HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805
 - 6 — O-RING MATERIAL: SILICONE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH			THIRD ANGLE PROJECTION	
CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE — — — — 6-12 LB		CONTACT ARRANGEMENT		DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE — — — 30 LB MAX		2X S P D T		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
RELEASE FORCE — — — — — 4 LB MIN		28 VDC		ONE PLACE (.) $\pm .030$
PRETRAVEL — — — — — .040 MAX		SEA LEVEL		TWO PLACE (.) $\pm .015$
DIFFERENTIAL TRAVEL — — — .020 MAX		50,000 FT.		THREE PLACE (.) $\pm .005$
OVERTRAVEL — — — — — .250 MIN				ANGLES $\pm$
				WEIGHT 5.6 OZ MAX
				ANSI Y14.5M-1982 APPLIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1EN42-R8](#)