

# Adjustable Constant Current Regulator & LED Driver

**45 V, 35 - 70 mA  $\pm$  15%, 1.5 W Package**

## NSI45035JZ, NSV45035JZ

The adjustable constant current regulator (CCR) is a simple, economical and robust device designed to provide a cost effective solution for regulating current in LEDs (similar to Constant Current Diode, CCD). The CCR is based on Self-Biased Transistor (SBT) technology and regulates current over a wide voltage range. It is designed with a negative temperature coefficient to protect LEDs from thermal runaway at extreme voltages and currents.

The CCR turns on immediately and is at 20% of regulation with only 0.5 V  $V_{AK}$ . The  $R_{adj}$  pin allows  $I_{reg(SS)}$  to be adjusted to higher currents by attaching a resistor between  $R_{adj}$  (Pin 3) and the Cathode (Pin 4). The  $R_{adj}$  pin can also be left open (No Connect) if no adjustment is required. It requires no external components allowing it to be designed as a high or low-side regulator. The high anode-cathode voltage rating withstands surges common in Automotive, Industrial and Commercial Signage applications. This device is available in a thermally robust package and is qualified to stringent AEC-Q101 standard, which is lead-free RoHS compliant and uses halogen-free molding compound, and UL94-V0 certified.

### Features

- Robust Power Package: 1.5 Watts
- Adjustable up to 70 mA
- Wide Operating Voltage Range
- Immediate Turn-On
- Voltage Surge Suppressing – Protecting LEDs
- AEC-Q101 Qualified and PPAP Capable, UL94-V0 Certified
- SBT (Self-Biased Transistor) Technology
- Negative Temperature Coefficient
- Eliminates Additional Regulation
- NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

### Applications


- Automobile: Chevron Side Mirror Markers, Cluster, Display & Instrument Backlighting, CHMSL, Map Light
- AC Lighting Panels, Display Signage, Decorative Lighting, Channel Lettering
- Switch Contact Wetting
- Application Note [AND8391/D](#) – Power Dissipation Considerations
- Application Note [AND8349/D](#) – Automotive CHMSL

$$I_{reg(SS)} = 35 - 70 \text{ mA}$$


$$@ V_{AK} = 7.5 \text{ V}$$



SOT-223  
CASE 318E  
STYLE 2



### MARKING DIAGRAM



A = Assembly Location  
Y = Year  
W = Work Week  
AAK = Specific Device Code  
▪ = Pb-Free Package

(Note: Microdot may be in either location)

### ORDERING INFORMATION

| Device        | Package           | Shipping <sup>†</sup> |
|---------------|-------------------|-----------------------|
| NSI45035JZT1G | SOT-223 (Pb-Free) | 1,000 / Tape & Reel   |
| NSV45035JZT1G | SOT-223 (Pb-Free) | 1,000 / Tape & Reel   |
| NSV45035JZT3G | SOT-223 (Pb-Free) | 4,000 / Tape & Reel   |

<sup>†</sup> For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, [BRD8011/D](#).

# NSI45035JZ, NSV45035JZ

## MAXIMUM RATINGS (T<sub>A</sub> = 25 °C unless otherwise noted)

| Symbol                            | Rating                                           | Value                                  | Unit |
|-----------------------------------|--------------------------------------------------|----------------------------------------|------|
| V <sub>AK</sub> Max               | Anode-Cathode Voltage                            | 45                                     | V    |
| V <sub>R</sub>                    | Reverse Voltage                                  | 500                                    | mV   |
| T <sub>J</sub> , T <sub>stg</sub> | Operating and Storage Junction Temperature Range | -55 to +150                            | °C   |
| ESD                               | ESD Rating:<br>Machine Model                     | Human Body Model<br>Class 2<br>Class C |      |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

## ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25 °C unless otherwise noted)

| Symbol                | Characteristic                                          | Min   | Typ | Max   | Unit |
|-----------------------|---------------------------------------------------------|-------|-----|-------|------|
| I <sub>reg(SS)</sub>  | Steady State Current @ V <sub>AK</sub> = 7.5 V (Note 1) | 29.75 | 35  | 40.25 | mA   |
| V <sub>overhead</sub> | Voltage Overhead (Note 2)                               |       | 1.8 |       | V    |
| I <sub>reg(P)</sub>   | Pulse Current @ V <sub>AK</sub> = 7.5 V (Note 3)        | 30.9  |     | 42.5  | mA   |
| C                     | Capacitance @ V <sub>AK</sub> = 7.5 V (Note 4)          |       | 7.4 |       | pF   |
| C                     | Capacitance @ V <sub>AK</sub> = 0 V (Note 4)            |       | 31  |       | pF   |

1. I<sub>reg(SS)</sub> steady state is the voltage (V<sub>AK</sub>) applied for a time duration ≥ 35 sec, using FR-4 @ 300 mm<sup>2</sup> 2 oz. Copper traces, in still air.
2. V<sub>overhead</sub> = V<sub>in</sub> - V<sub>LEDs</sub>. V<sub>overhead</sub> is typical value for 75% I<sub>reg(SS)</sub>.
3. I<sub>reg(P)</sub> non-repetitive pulse test. Pulse width t ≤ 1.0 msec.
4. f = 1 MHz, 0.02 V RMS.

## THERMAL CHARACTERISTICS

| Symbol                            | Characteristic                                                                  | Max           | Unit        |
|-----------------------------------|---------------------------------------------------------------------------------|---------------|-------------|
| P <sub>D</sub>                    | Total Device Dissipation (Note 5) T <sub>A</sub> = 25 °C<br>Derate above 25 °C  | 1008<br>8.06  | mW<br>mW/°C |
| R <sub>θJA</sub>                  | Thermal Resistance, Junction-to-Ambient (Note 5)                                | 124           | °C/W        |
| R <sub>ψJL4</sub>                 | Thermal Reference, Junction-to-Lead 4 (Note 5)                                  | 33.3          | °C/W        |
| P <sub>D</sub>                    | Total Device Dissipation (Note 6) T <sub>A</sub> = 25 °C<br>Derate above 25 °C  | 1136<br>9.09  | mW<br>mW/°C |
| R <sub>θJA</sub>                  | Thermal Resistance, Junction-to-Ambient (Note 6)                                | 110           | °C/W        |
| R <sub>ψJL4</sub>                 | Thermal Reference, Junction-to-Lead 4 (Note 6)                                  | 33.3          | °C/W        |
| P <sub>D</sub>                    | Total Device Dissipation (Note 7) T <sub>A</sub> = 25 °C<br>Derate above 25 °C  | 1238<br>9.9   | mW<br>mW/°C |
| R <sub>θJA</sub>                  | Thermal Resistance, Junction-to-Ambient (Note 7)                                | 101           | °C/W        |
| R <sub>ψJL4</sub>                 | Thermal Reference, Junction-to-Lead 4 (Note 7)                                  | 33.7          | °C/W        |
| P <sub>D</sub>                    | Total Device Dissipation (Note 8) T <sub>A</sub> = 25 °C<br>Derate above 25 °C  | 1420<br>11.36 | mW<br>mW/°C |
| R <sub>θJA</sub>                  | Thermal Resistance, Junction-to-Ambient (Note 8)                                | 88            | °C/W        |
| R <sub>ψJL4</sub>                 | Thermal Reference, Junction-to-Lead 4 (Note 8)                                  | 32.1          | °C/W        |
| P <sub>D</sub>                    | Total Device Dissipation (Note 9) T <sub>A</sub> = 25 °C<br>Derate above 25 °C  | 1316<br>10.53 | mW<br>mW/°C |
| R <sub>θJA</sub>                  | Thermal Resistance, Junction-to-Ambient (Note 9)                                | 95            | °C/W        |
| R <sub>ψJL4</sub>                 | Thermal Reference, Junction-to-Lead 4 (Note 9)                                  | 32.4          | °C/W        |
| P <sub>D</sub>                    | Total Device Dissipation (Note 10) T <sub>A</sub> = 25 °C<br>Derate above 25 °C | 1506<br>12.05 | mW<br>mW/°C |
| R <sub>θJA</sub>                  | Thermal Resistance, Junction-to-Ambient (Note 10)                               | 83            | °C/W        |
| R <sub>ψJL4</sub>                 | Thermal Reference, Junction-to-Lead 4 (Note 10)                                 | 30.8          | °C/W        |
| T <sub>J</sub> , T <sub>stg</sub> | Junction and Storage Temperature Range                                          | -55 to +150   | °C          |

NOTE: Lead measurements are made by non-contact methods such as IR with treated surface to increase emissivity to 0.9.

Lead temperature measurement by attaching a T/C may yield values as high as 30% higher °C/W values based upon empirical measurements and method of attachment.

5. FR-4 @ 300 mm<sup>2</sup>, 1 oz. copper traces, still air.
6. FR-4 @ 300 mm<sup>2</sup>, 2 oz. copper traces, still air.
7. FR-4 @ 500 mm<sup>2</sup>, 1 oz. copper traces, still air.
8. FR-4 @ 500 mm<sup>2</sup>, 2 oz. copper traces, still air.
9. FR-4 @ 700 mm<sup>2</sup>, 1 oz. copper traces, still air.
10. FR-4 @ 700 mm<sup>2</sup>, 2 oz. copper traces, still air.

TYPICAL PERFORMANCE CURVES

MINIMUM FR-4 @ 300 MM<sup>2</sup>, 2 OZ COPPER TRACE, STILL AIR




Figure 1. General Performance Curve for CCR




Figure 2. Steady State Current ( $I_{reg(SS)}$ ) vs. Anode-Cathode Voltage ( $V_{ak}$ )




Figure 3. Pulse Current ( $I_{reg(P)}$ ) vs. Anode-Cathode Voltage ( $V_{ak}$ )




Figure 4. Steady State Current vs. Pulse Current Testing




Figure 5. Current Regulation vs. Time





Figure 6.  $I_{reg(SS)}$  vs.  $R_{adj}$

## NSI45035JZ, NSV45035JZ



**Figure 7. Power Dissipation vs. Ambient Temperature @  $T_J = 150^\circ\text{C}$**

## APPLICATIONS INFORMATION


The CCR is a self biased transistor designed to regulate the current through itself and any devices in series with it. The device has a slight negative temperature coefficient, as shown in Figure 2 – Tri Temp. (i.e. if the temperature increases the current will decrease). This negative temperature coefficient will protect the LEDs by reducing the current as temperature rises.

The CCR turns on immediately and is typically at 20% of regulation with only 0.5 V across it.

The device is capable of handling voltage for short durations of up to 45 V so long as the die temperature does not exceed  $150^\circ\text{C}$ . The determination will depend on the thermal pad it is mounted on, the ambient temperature, the pulse duration, pulse shape and repetition.

### Single LED String

The CCR can be placed in series with LEDs as a High Side or a Low Side Driver. The number of the LEDs can vary from one to an unlimited number. The designer needs to calculate the maximum voltage across the CCR by taking the maximum input voltage less the voltage across the LED string (Figures 8 and 9).



**Figure 8.**




Figure 9.




Figure 11.

### Higher Current LED Strings

Two or more fixed current CCRs can be connected in parallel. The current through them is additive (Figure 10).




Figure 10.

### Other Currents

The adjustable CCR can be placed in parallel with any other CCR to obtain a desired current. The adjustable CCR provides the ability to adjust the current as LED efficiency increases to obtain the same light output (Figure 11).

### Dimming using PWM

The dimming of an LED string can be easily achieved by placing a BJT in series with the CCR (Figure 12).





Figure 12.

The method of pulsing the current through the LEDs is known as Pulse Width Modulation (PWM) and has become the preferred method of changing the light level. LEDs being a silicon device, turn on and off rapidly in response to the current through them being turned on and off. The switching time is in the order of 100 nanoseconds, this equates to a maximum frequency of 10 Mhz, and applications will typically operate from a 100 Hz to 100 kHz. Below 100 Hz the human eye will detect a flicker from the light emitted from the LEDs. Between 500 Hz and 20 kHz the circuit may


generate audible sound. Dimming is achieved by turning the LEDs on and off for a portion of a single cycle. This on/off cycle is called the Duty cycle (D) and is expressed by the amount of time the LEDs are on (T<sub>ON</sub>) divided by the total time of an on/off cycle (T<sub>s</sub>) (Figure 13).



**Figure 13.**

The current through the LEDs is constant during the period they are turned on resulting in the light being consistent with no shift in chromaticity (color). The brightness is in proportion to the percentage of time that the LEDs are turned on.

Figure 14 is a typical response of Luminance vs Duty Cycle.



**Figure 14. Luminous Emittance vs. Duty Cycle**

### Reducing EMI

Designers creating circuits switching medium to high currents need to be concerned about Electromagnetic Interference (EMI). The LEDs and the CCR switch extremely fast, less than 100 nanoseconds. To help eliminate EMI, a capacitor can be added to the circuit across R2. (Figure 12) This will cause the slope on the rising and falling edge on the current through the circuit to be extended. The slope of the CCR on/off current can be controlled by the values of R1 and C1.

The selected delay / slope will impact the frequency that is selected to operate the dimming circuit. The longer the delay, the lower the frequency will be. The delay time should not be less than a 10:1 ratio of the minimum on time. The frequency is also impacted by the resolution and dimming steps that are required. With a delay of 1.5 microseconds on the rise and the fall edges, the minimum on time would be 30 microseconds. If the design called for a resolution of 100 dimming steps, then a total duty cycle time (T<sub>s</sub>) of 3 milliseconds or a frequency of 333 Hz will be required.

**Thermal Considerations**


As power in the CCR increases, it might become necessary to provide some thermal relief. The maximum power dissipation supported by the device is dependent upon board design and layout. Mounting pad configuration on the PCB, the board material, and the ambient temperature affect the rate of junction temperature rise for the part. When the device has good thermal conductivity through the PCB, the junction temperature will be relatively low with high power applications. The maximum dissipation the device can handle is given by:

$$P_{D(MAX)} = \frac{T_{J(MAX)} - T_A}{R_{\theta JA}}$$

Referring to the thermal table on page 2 the appropriate  $R_{\theta JA}$  for the circuit board can be selected.

**AC Applications**

The CCR is a DC device; however, it can be used with full wave rectified AC as shown in application notes [AND8433/D](#) and [AND8492/D](#) and design notes [DN05013/D](#) and [DN06065/D](#). Figure 15 shows the basic circuit configuration.



**Figure 15. Basic AC Application**

## NSI45035JZ, NSV45035JZ

### REVISION HISTORY

| Revision | Description of Changes                            | Date      |
|----------|---------------------------------------------------|-----------|
| 4        | Rebranded the Data Sheet to <b>onsemi</b> format. | 9/04/2025 |

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.



**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)