







Loading-Plan:



-Transmission properties in accordance with ISO/IEC 11801:2002: Class D.
 -Protection level: IP20
 -Temperature range: -40°C ...+70°C

 All Dimensions in mm Original Size DIN A 3			Techn. Character.				Nicht tolerierte Maß/Free size tolerances				
				Dat.	Name	Maßstab/Scale 2:1 (1:1)	RJ45 cord IP20, 90° angled overmoulding 2xRJ45, 90°+270° Position, CAT5				
			Detail.	14.10.05	MR						
			Insp.	14.10.05	RA						
DRS490A	07.04.09	MS	Stand.								
32762	15.12.05	MS	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP					TB 09 47 03 04 0xx			Blatt/ page 1 2
32756											
Mod.	Dat.	Name					Sub.				

	1	2	3	4	5	6	7	8	
A	cont-No.	Part-No.	Type of cable	Dim. a		cont-No.	Part-No.	Type of cable	Dim. a
	1	09 47 03 04 001	AWG 22/1 solid	0,5 m		51	09 47 03 04 051	AWG 22/7 trailing	5 m
	2	09 47 03 04 002	AWG 22/1 solid	1 m		52	09 47 03 04 052	AWG 22/7 trailing	6 m
	3	09 47 03 04 003	AWG 22/1 solid	1,5 m		53	09 47 03 04 053	AWG 22/7 trailing	7 m
	4	09 47 03 04 004	AWG 22/1 solid	2 m		54	09 47 03 04 054	AWG 22/7 trailing	8 m
	5	09 47 03 04 005	AWG 22/1 solid	3 m		55	09 47 03 04 055	AWG 22/7 trailing	9 m
	6	09 47 03 04 006	AWG 22/1 solid	4 m		56	09 47 03 04 056	AWG 22/7 trailing	10 m
	7	09 47 03 04 007	AWG 22/1 solid	5 m		57	09 47 03 04 057	AWG 22/7 trailing	15 m
	8	09 47 03 04 008	AWG 22/1 solid	6 m		58	09 47 03 04 058	AWG 22/7 trailing	20 m
	9	09 47 03 04 009	AWG 22/1 solid	7 m		59	09 47 03 04 059	AWG 22/7 trailing	30 m
B	10	09 47 03 04 010	AWG 22/1 solid	8 m		60	09 47 03 04 060	AWG 22/7 trailing	40 m
	11	09 47 03 04 011	AWG 22/1 solid	9 m		61	09 47 03 04 061	AWG 22/7 trailing	50 m
	12	09 47 03 04 012	AWG 22/1 solid	10 m		62	09 47 03 04 062	AWG 22/7 trailing	60 m
	13	09 47 03 04 013	AWG 22/1 solid	15 m		63	09 47 03 04 063	AWG 22/7 trailing	70 m
	14	09 47 03 04 014	AWG 22/1 solid	20 m		64	09 47 03 04 064	AWG 22/7 trailing	80 m
	15	09 47 03 04 015	AWG 22/1 solid	30 m		65	09 47 03 04 065	AWG 22/7 trailing	90 m
	16	09 47 03 04 016	AWG 22/1 solid	40 m		66	09 47 03 04 066	AWG 22/7 trailing	100 m
	17	09 47 03 04 017	AWG 22/1 solid	50 m		67	09 47 03 04 067	AWG 22/7 "outdoor"	0,5 m
	18	09 47 03 04 018	AWG 22/1 solid	60 m		68	09 47 03 04 068	AWG 22/7 "outdoor"	1 m
	19	09 47 03 04 019	AWG 22/1 solid	70 m		69	09 47 03 04 069	AWG 22/7 "outdoor"	1,5 m
C	20	09 47 03 04 020	AWG 22/1 solid	80 m		70	09 47 03 04 070	AWG 22/7 "outdoor"	2 m
	21	09 47 03 04 021	AWG 22/1 solid	90 m		71	09 47 03 04 071	AWG 22/7 "outdoor"	3 m
	22	09 47 03 04 022	AWG 22/1 solid	100 m		72	09 47 03 04 072	AWG 22/7 "outdoor"	4 m
	23	09 47 03 04 023	AWG 22/7 stranded	0,5 m		73	09 47 03 04 073	AWG 22/7 "outdoor"	5 m
	24	09 47 03 04 024	AWG 22/7 stranded	1 m		74	09 47 03 04 074	AWG 22/7 "outdoor"	6 m
	25	09 47 03 04 025	AWG 22/7 stranded	1,5 m		75	09 47 03 04 075	AWG 22/7 "outdoor"	7 m
	26	09 47 03 04 026	AWG 22/7 stranded	2 m		76	09 47 03 04 076	AWG 22/7 "outdoor"	8 m
	27	09 47 03 04 027	AWG 22/7 stranded	3 m		77	09 47 03 04 077	AWG 22/7 "outdoor"	9 m
	28	09 47 03 04 028	AWG 22/7 stranded	4 m		78	09 47 03 04 078	AWG 22/7 "outdoor"	10 m
D	29	09 47 03 04 029	AWG 22/7 stranded	5 m		79	09 47 03 04 079	AWG 22/7 "outdoor"	15 m
	30	09 47 03 04 030	AWG 22/7 stranded	6 m		80	09 47 03 04 080	AWG 22/7 "outdoor"	20 m
	31	09 47 03 04 031	AWG 22/7 stranded	7 m		81	09 47 03 04 081	AWG 22/7 "outdoor"	30 m
	32	09 47 03 04 032	AWG 22/7 stranded	8 m		82	09 47 03 04 082	AWG 22/7 "outdoor"	40 m
	33	09 47 03 04 033	AWG 22/7 stranded	9 m		83	09 47 03 04 083	AWG 22/7 "outdoor"	50 m
	34	09 47 03 04 034	AWG 22/7 stranded	10 m		84	09 47 03 04 084	AWG 22/7 "outdoor"	60 m
	35	09 47 03 04 035	AWG 22/7 stranded	15 m		85	09 47 03 04 085	AWG 22/7 "outdoor"	70 m
	36	09 47 03 04 036	AWG 22/7 stranded	20 m		86	09 47 03 04 086	AWG 22/7 "outdoor"	80 m
	37	09 47 03 04 037	AWG 22/7 stranded	30 m		87	09 47 03 04 087	AWG 22/7 "outdoor"	90 m
E	38	09 47 03 04 038	AWG 22/7 stranded	40 m		88	09 47 03 04 088	AWG 22/7 "outdoor"	100 m
	39	09 47 03 04 039	AWG 22/7 stranded	50 m					
	40	09 47 03 04 040	AWG 22/7 stranded	60 m					
	41	09 47 03 04 041	AWG 22/7 stranded	70 m					
	42	09 47 03 04 042	AWG 22/7 stranded	80 m					
	43	09 47 03 04 043	AWG 22/7 stranded	90 m					
	44	09 47 03 04 044	AWG 22/7 stranded	100 m					
	45	09 47 03 04 045	AWG 22/7 trailing	0,5 m					
	46	09 47 03 04 046	AWG 22/7 trailing	1 m					
	47	09 47 03 04 047	AWG 22/7 trailing	1,5 m					
F	48	09 47 03 04 048	AWG 22/7 trailing	2 m					
	49	09 47 03 04 049	AWG 22/7 trailing	3 m					
	50	09 47 03 04 050	AWG 22/7 trailing	4 m					

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maße/Free size tolerances		
				Dat.	Name	Maßstab/Scale 2:1 (1:1)	RJ45 cord IP20, 90° angled overmoulding 2xRJ45, 90°+270° Position, CAT5	
			Detail.	14.10.05	MR			
			Insp.	14.10.05	RA			
			Stand.					
DRS490A	07.04.09	MS	HARTING Electronics GmbH & Co. KG				TB 09 47 03 04 0xx	
32762	15.12.05	MS	D-32339 ESPELKAMP					
32756								
Mod.	Dat.	Name					Blatt/ page 2/2	