

v02.0705




## HBT DIGITAL PHASE-FREQUENCY DETECTOR, 10 - 1300 MHz

#### Typical Applications

This Phase Frequency Detector is a key component in low phase noise frequency synthesis applications such as:

- Point-to-Point Radios
- Satellite Communication Systems
- Military Applications
- Sonet Clock Generation

#### **Functional Diagram**



#### **Features**

Ultra Low SSB Phase Noise Floor:
-153 dBc/Hz @ 10 kHz offset @ 100 MHz
Input up to 1300 MHz Fin.

Differential Input/Single Ended Output

Open Collector Output Buffer Amplifiers

QSOP16G SMT Package: 29.4 mm<sup>2</sup>

#### **General Description**

The HMC439QS16G & HMC439QS16GE are digital phase-frequency detectors intended for use in low noise phase-locked loop applications for inputs from 10 to 1300 MHz. Its combination of high frequency of operation along with its ultra low phase noise floor make possible synthesizers with wide loop bandwidth and low N resulting in fast switching and very low phase noise. When used in conjunction with a differential loop amplifier, the HMC439QS16G & HMC439QS16GE generate output voltages that can be used to phase lock a VCO to a reference oscillator. The device is packaged in a low cost, surface mount 16 lead QSOP package with an exposed base for improved RF and thermal performance.

## Electrical Specifications, $T_{\Delta} = +25^{\circ}$ C, Vcc=5V

Parameter	Conditions	Min.	Тур.	Max.	Units
Maximum Input Frequency		1300			MHz
Minimum Input Frequency	Sine Wave Input			10	MHz
Input Power Range	Fin= 10 to 1300 MHz	-10		+10	dBm
Output Voltage			2000		mV, Pk - Pk
SSB Phase Noise	@ 10 kHz Offset with 100 MHz Input & Pin= 0 dBm		-153		dBc/Hz
Supply Current (Icc)			96		mA

## HMC439\* PRODUCT PAGE QUICK LINKS

Last Content Update: 02/23/2017

## COMPARABLE PARTS -

View a parametric search of comparable parts.

## **EVALUATION KITS**

· HMC439QS16G Evaluation Board.

### **DOCUMENTATION**

#### **Data Sheet**

• HMC439 Data Sheet

#### TOOLS AND SIMULATIONS •

 Using the HMC Design Tool for Synthesizers with a PFD Output

## REFERENCE MATERIALS 🖵

#### **Quality Documentation**

- HMC Legacy PCN: QS##, QS##E and QS##G,QS##GE packages - Relocation of pre-existing production equipment to new building
- Package/Assembly Qualification Test Report: Plastic Encapsulated QSOP (QTR: 02015 REV: 11)
- PCN: MS, QS, SOT, SOIC packages Sn/Pb plating vendor change
- Semiconductor Qualification Test Report: GaAs HBT-A (QTR: 2013-00228)

## DESIGN RESOURCES 🖵

- HMC439 Material Declaration
- PCN-PDN Information
- · Quality And Reliability
- Symbols and Footprints

#### **DISCUSSIONS**

View all HMC439 EngineerZone Discussions.

#### SAMPLE AND BUY 🖳

Visit the product page to see pricing options.

## **TECHNICAL SUPPORT**

Submit a technical question or find your regional support number.

#### DOCUMENT FEEDBACK $\Box$

Submit feedback for this data sheet.




v02.0705




## HBT DIGITAL PHASE-FREQUENCY DETECTOR, 10 - 1300 MHz


#### Error Voltage vs. Frequency, Pin= 0 dBm\*




#### Error Voltage vs. Supply Voltage, Pin= 0 dBm, Fin= 250 MHz\*




#### Error Voltage vs. Temperature, Pin= 0 dBm, Fin= 250 MHz\*



#### SSB Phase Noise Performance, Pin= 0 dBm, T= 25 °C



#### SSB Phase Noise Performance, Pin= 0 dBm, Fin= 100 MHz



<sup>\*</sup> See Gain & Error Voltage Test Circuit herein.



v02.0705



# HBT DIGITAL PHASE-FREQUENCY DETECTOR, 10 - 1300 MHz

### **Absolute Maximum Ratings**

RF Input (Vcc= +5V)	+13 dBm
Supply Voltage (Vcc)	+5.5V
Channel Temperature (Tc)	135 °C
Continuous Pdiss (T = 85 °C) (derate 47.2 mW/° C above 85 °C)	4.25 W
Storage Temperature	-65 to +150 °C
Operating Temperature	-40 to +85 °C



ELECTROSTATIC SENSITIVE DEVICE OBSERVE HANDLING PRECAUTIONS

#### Typical Supply Current vs. Vcc


Vcc (Vdc)	Icc (mA)
4.8	90
5.0	96
5.2	102


Note: Detector will work over full voltage range above.


## Typical DC Characteristics @ Vcc = +5V

Cumbal	Characteristics	+25C			11-14-
Symbol		Min.	Тур.	Max.	Units
Icc	Power Supply Current	90	96	102	mA
Voh	Output High Voltage	5.0	5.0	5.0	V
Vol	Output Low Voltage	2.9	3	3.1	V

### **Outline Drawing**







#### NOTES:

- 1. LEADFRAME MATERIAL: COPPER ALLOY
- 2. DIMENSIONS ARE IN INCHES [MILLIMETERS]
- ⚠ DIMENSION DOES NOT INCLUDE MOLDFLASH OF 0.15mm PER SIDE.
- A DIMENSION DOES NOT INCLUDE MOLDFLASH OF 0.25mm PER SIDE.
- 5. ALL GROUND LEADS AND GROUND PADDLE MUST BE SOLDERED TO PCB RF GROUND.

#### Package Information

Part Number	Package Body Material	Lead Finish	MSL Rating	Package Marking [3]
HMC439QS16G	Low Stress Injection Molded Plastic	Sn/Pb Solder	MSL1 [1]	H439 XXXX
HMC439QS16GE	RoHS-compliant Low Stress Injection Molded Plastic	100% matte Sn	MSL1 [2]	H439 XXXX

- [1] Max peak reflow temperature of 235 °C
- [2] Max peak reflow temperature of 260  $^{\circ}\text{C}$
- [3] 4-Digit lot number XXXX

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.



v02.0705



## HBT DIGITAL PHASE-FREQUENCY DETECTOR, 10 - 1300 MHz

#### **Pin Description**

Pin Number	Function	Description	Interface Schematic
1	Vcc	Supply voltage 5V ± 0.2V	
2, 8, 9, 11, 16	GND	All ground leads and ground paddle must be connected to PCB RF/DC ground.	<u> </u>
		(These pins are AC coupled and must be DC blocked externally.)	Vcc o
3	REF	Reference Input	NREF O D 10 mA
4	NREF	Reference Input Compliment	
5	N/C	Not Connected	
		(These pins are AC coupled and must be DC blocked externally.)	Vcc o
6	vco	VCO Input	VC0 0 500 NVC0 0
7	NVCO	VCO Input Compliment	10 mA
10	Vcc3V	3.0 Volt Reference Voltage for Internal 10mA Current Source	Vcc3V 20∩ ↓ 10 mA
12	ND	Down Output Compliment	ND D
13	D	Down Output	① 10 mA
			NU U
14	NU	Up Output Compliment	
15	U	Up Output	① 10 mA

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

For price, delivery, and to place orders: Analog Devices, Inc., One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106 Phone: 781-329-4700 • Order online at www.analog.com Application Support: Phone: 1-800-ANALOG-D




v02.0705



# HBT DIGITAL PHASE-FREQUENCY DETECTOR, 10 - 1300 MHz

#### Gain & Error Voltage Test Circuit:


Gain & Error Voltage data taken using test circuit below. Loop filter gain has been subtracted from the result.



 $\Delta F$ = The beat frequency of the sawtooth waveform.

#### Typical PLL Application Circuit using HMC439QS16G

PLL application shown for a 12.8 GHz Fout. Contact HMC to discuss your specific application.






v02.0705



# HBT DIGITAL PHASE-FREQUENCY DETECTOR, 10 - 1300 MHz

#### **Evaluation PCB**



The circuit board used in the final application should use RF circuit design techniques. Signal lines should have 50 ohm impedance while the package ground leads and backside ground slug should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Hittite upon request.

## List of Materials for Evaluation PCB 105809 [1]

Item	Description
J1 - J4	PCB Mount SMA RF Connector
J5	2 mm DC Header
C1	4.7 μF Capacitor
C2, C5 - C7	100 pF Capacitor, 0402 Pkg.
C3, C4, C8	1000 pF Capacitor, 0603 Pkg.
R1 <sup>[3]</sup> , R2 <sup>[3]</sup>	4.3 Ohm Resistor, 0603 Pkg.
R3, R4, R5	200 Ohm Resistor, 0603 Pkg.
U1	HMC439QS16G / HMC439QS16GE
PCB [2]	105733 Eval Board

[1] Reference this number when ordering complete evaluation PCB

[2] Circuit Board Material: Rogers 4350

[3] Choose values of R1 & R2 between 4.3 and 20 Ohms for best noise performance

#### **Evaluation PCB Circuit**

