






FEMALE END VIEW (J1)	MALE END VIEW (P1,P2)	WIRING DIAGRAM	SPECIFICATIONS	
			CONTACT CARRIER MATERIAL/COLOR	NYLON OR TPU/BLACK
			MOLDED HEAD MATERIAL/COLOR	TPU/BLACK
			CONTACT MATERIAL/PLATING	BRASS/GOLD
			COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
			RATED CURRENT [A]	150 mA (PINS 2,4), 4.0 A (PINS 1,3,5)
			RATED VOLTAGE [V]	150 V (PINS 2,4), 250 V (PINS 1,3,5)
			TEMPERATURE RATING	-40°C to +105°C (-40°F to +221°F)
			PROTECTION CLASS	MEETS IEC IP60
			RIGHT-ANGLE CORDSET DIRECTION SYMBOL	



					RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. TURCK INC <i>High Technology Sensors and Automation Controls</i> 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com					
					1. 2. 3. 4.									
					MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT CBM		DATE 12/18/98		DESCRIPTION VB2-FSW/FKW/FSW 45	
									DSGN GC		SCALE 1=1.0			
					FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT		IDENTIFICATION NO.		REV	
									MILLIMETER [INCH]		U0095-2		G	
									DO NOT SCALE THIS DRAWING		FILE: U0095-2		SHEET 1 OF 1	
G	DRAWING PROCESSED AS PART OF ECO 33971			CBM	04/07/11	33971								
REV	DESCRIPTION			BY	DATE	ECO NO.								