


REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12



NOTES:

Insulator Material: Nylon-6T, UL 94V-0

Contact Plating: TIN, 80-100μ"

Contact Material: Brass

Current Rating : 1A AC,DC




Contact Resistance: 20MΩ Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ

Min.

Operating Temp.: -40° C~+105° C



NUMBER OF POSITIONS	DIMENSIONS		
	A	B	C
10	5.08	11.25	12.65
14	7.62	13.79	15.19
16	8.89	15.06	16.46
20	11.43	17.60	19.00
26	15.24	21.41	22.81
30	17.78	23.95	25.35
34	20.32	26.49	27.89
40	24.13	30.30	31.70
50	30.48	36.65	38.05
60	36.83	43.00	44.40

UNLESS TOLERANCE		DRAW BY		Cnc Tech,LLC	
GENERAL	ANGLE	DESIGN BY			
X. ± 0.30	X.° ± 3.0°	CHECK BY			
.X ± 0.25	.X° ± 2.0°	APPROVE BY			
.XX ± 0.20	.XX° ± 1.0°			Part NO. 3220-XX-0300-99	
.XXX ± 0.10	.XXX ± 0.5°				
SCALE		SHEET	UNIT	DRAW NO:	
1:1		1/1	MM		
					