



REV.	DATE	DESCRIPTION
A	06/25/98	REVISIONS MADE TO CONNECTOR
B	01/27/00	REVISE INSULATOR, CONTACT PIN
C	07/28/06	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						07/28/06
7	HEAT SHRINK			1		CHECKED							
6	FERRULE	COPPER	GOLD	1			ISSUED		PART DESCRIPTION SMA CRIMP PLUG (FOR RG-178B/U, 196A/U, CABLE)				
5	HEX NUT	BRASS	GOLD	1			SHEET	1 OF 1					
4	BARREL	BRASS	GOLD	1					PART NO. 132193				
3	CONTACT PIN	BRASS	GOLD	1									
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO. 132193.DWG					
1	BODY	BRASS	GOLD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE	C:/132/132193.DWG	REV.	C	SIZE	A	SCALE	NA