

Nominal Voltage (V)	3
Nominal Capacity (mAh) ^{*1}	1600
Standard Discharge Current (mA)	5
Max. Discharge Current (mA)	Continuous ^{*2} 500
	Pulse ^{*3} 2500
Operating Temperature Range (°C)	-40 ~ +85
Max. Dimensions (mm)	Diameter (D) 17.0
	Height (H) 33.5
Weight (g)	17


*1 Nominal capacity is determined at an end voltage of 2.0V when the battery is allowed to discharge at a standard current level at +23°C.

*2 Current value is determined to be the level at which 50% of the nominal capacity is obtained with an end voltage of 2.0V at +23°C.


*3 Current value for obtaining 1.0V cell voltage when pulse is applied for 15 seconds at 50% discharge depth (50% of the nominal capacity) at +23°C.

Typical Characteristics


Temperature Characteristics of CR17335E-R



Temperature Characteristics of CR17335E-R



Discharge Characteristics after storage of CR17335E-R



Discharge Load vs. Cell Capacity of CR17335E-R

