





PANEL THICKNESS	X dimension
0.75-1.25 [.030-.049]	19.2-.01 [.756]
1.25-2.0 [.049-.079]	19.4-.01 [.764]
2.0-3.0 [.079-.118]	19.8-.01 [.780]



NOTES:


1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. RATING:
6A @250VAC;9A @125VAC (UL, CSA, VDE)
4. MATERIAL:
4(1)A @250VAC

CIRCUIT: DPST



- CONTACT SURFACE: Coin Silver, Silver Plate
- TERMINAL: Copper Alloy W/ Silver Plate.
- CONTACT RESISTANCE: 20mILLOHMS TYP. INITIAL
- INSULATION RESISTANCE: 1000MegOOHMS
- DIELECTRIC STRENGTH:
>1500V RMS min. @SEA LEVEL
>3000V RMS @SEA LEVEL
- MECHANICAL LIFE: 50,000 CYCLES.
- ELECTRICAL LIFE: 10,000 CYCLES.

RECOMMENDED P.C.B. HOLES



TITLE			
B	11330	REVISED AND REDRAWN	10/3/01 CJB
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE		DATE	DR
1.5:1		10/03/01	CB
DWG		REV	
M400015		B	