






4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT - By -				ALL RIGHTS RESERVED.				
LOC G		DIST 14		REVISIONS				
P		LTR		DESCRIPTION		DATE	DWN	APVD
		M1		REVISED PER ECO-14-001427		29JAN2014	NK	DR




STAMPING DETAIL



1 FOR 7.62[.300] MAX WIRE INSULATION DIAMETER.

50	LOOSE PC, BOX	8-34865-2
500	LOOSE PC	34865
QTY	DESCRIPTION	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 90°C [194°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G KRUPER 1/93		 TE Connectivity						
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300V MAX		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:					CHK R HERSEY 1/93		
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		WIRE: 2.62-6.64mm² [5180-13100] SOLID OR STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -					APVD M CLINE 1/93		
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL BODY: COPPER INSULATION: PVC COLOUR: YELLOW		FINISH SPLICED: TIN PLATED ASTM B545					PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		
CUSTOMER DRAWING										SCALE 4:1		SHEET 1 OF 1		REV M1	